




- 1 WIRE INSULATION ϕ 2.032[ϕ .080] TO ϕ 3.175[ϕ .125].
- 2 FINISH:
BODY AND SLEEVE: TIN/LEAD (93-7) PLATE PER
ASTM B545.(3% MIN LEAD CONTENT)
INSULATION: COLOR-NATURAL.
- 3 MATERIAL:
BODY AND SLEEVE: COPPER PER ASTM B152
INSULATION: PVF²
- 4 STAMP AMP 22-18* APPROX AS SHOWN.
22-16 TERMINALS ARE STAMPED
22-18 IN ACCORDANCE WITH
MILITARY SPEC SAE AS 7928.
COMMERCIAL WIRE RANGE IS 22-16.

M7928/6-3 CLASS 2	2500	ON TAPE	53548-2
M7928/6-3 CLASS 1 & 2	1000	LOOSE PIECE	53548-1
MILITARY PART NUMBER & CLASS	QTY	PACKAGE TYPE	PART NO.

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 150°C[302°F]	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S.S. GOULDEN 9-28-93	TE Connectivity			
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: -	DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK R. HERSEY 9-28-93				
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	CIRCULAR MIL AREA: 0.26-1.65mm² [509-3,260] STRANDED		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.127[.005] 4 PLC ± - ANGLES ± -	APVD M ELLIS 9-28-93	NAME SPLICE, BUTT,PVF ² , P.I.D.G., WIRE SIZE: 22-16 AWG			
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		FINISH	PRODUCT SPEC -	APPLICATION SPEC 114-2157	SIZE A3	CAGE CODE 00779	DRAWING NO C=53548
			MATERIAL 		WEIGHT -	RESTRICTED TO -			
CUSTOMER DRAWING						SCALE 1:1	SHEET 1 OF 1	REV K1	