


LOC	DIST	REVISIONS				
CE	16	P	LTR	DESCRIPTION	DATE	APVD
			D	REV PER EC A40-0163-02	26APR02	ADB SM

1. DIMENSIONS IN [] ARE IN INCHES.

2. MAXIMUM INSERTION LOSS IS 0.5dB PLUS CABLE ATTENUATION OF 1.5dB/km AT 1300nm.



3.50	2000±20 [78740±787]	9-504970-9
1.33	550±5 [21653±197]	9-504970-8
0.52	13.72±0.15 [540±6]	1-504970-1
0.52	12.19±0.15 [480±6]	1-504970-0
0.52	10.67±0.15 [420±6]	504970-9
0.51	6.1±0.08 [240±3]	504970-8
0.53	20±0.3 [787±12]	504970-7
0.52	15±0.15 [591±6]	504970-6
0.52	10±0.15 [394±6]	504970-5
0.51	5±0.08 [197±3]	504970-4
0.50	3±0.05 [118±2]	504970-3
0.50	2±0.05 [79±2]	504970-2
0.50	1±0.05 [39±2]	504970-1
MAX IL (dB)	L	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S.URICH 20APR99	AMP AMP Incorporated Harrisburg, PA 17105-3608		
DIMENSIONS: METERS ■ [INCHES]		CHK R.PAUL 23APR96			
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -	APVD N.MILLER 24APR96	NAME CABLE ASSY, FIBER OPTIC, 62.5/125µm LDS, AMP SC (NG) TO AMP SC (NG), OPTIMATE		
		PRODUCT SPEC	SIZE CAGE CODE DRAWING NO RESTRICTED TO		
		APPLICATION SPEC	A3 00779 C-504970		
MATERIAL -	FINISH -	WEIGHT -	CUSTOMER DRAWING		
		SCALE NTS	SHEET 1 OF 1	REV D	