

© 1966 BY AMP INCORPORATED. ALL RIGHTS RESERVED. AMP PRODUCTS ARE COVERED BY PATENTS AND/OR PATENT PENDING.


Unauthorized reproduction or use of this drawing without written permission of AMP INCORPORATED is prohibited.

NUMBER 50719

S

C

B



TONGUE MATERIAL THK = .048 ±.003

50719-6	1.504	.679	.515 ±.005	1/2	OBsolete
50719-5	1.415	.500	.445 ±.003	6	OBsolete
50719-4			.453 ±.005	7/16	OBsolete
50719-3	1.504	.679	.390 ±.005	3/8	
50719-2			.328 ±.005	5/16	
50719-1			.265 ±.005	1/4	
50719	1.415	.500	.197 ±.003	10	
PART NO.	"A"	"B"	"C"	"D"	

AMP 1470-1 (11/64) 5

REVISIONS				
ZONE	LTR	DESCRIPTION	DATE	APPROVED
	O	PER NPS. 66-1760-1764	11-15-66	ST
	A	REMOVED ENGRG CONT PER REV NPS 66-1760-1764	7/10/67	RHW
	B	REV TITLE PER ECN PC-5545	12-6-68	RHW
	C	ADDED 50719-5 NPS 69-0554	12-16-69	Jwa
	D	ADDED 50719-6 NPS 75-1756	6-17-75	Jwa
	E	REVISED PER G-1651	11/8/85	pm
	F	OBsolete - 4 #6 G-2508	7/23/87	pm
	G	OBs - 5 PER S-2856	8/3/88	W.S.V.

TABLE I

1	WIRE TERMINAL	SEE TABLE II	INSERT: BRASS (MIL-C-50) TIN PL (MIL-T-10727) TYPE I .0003 MIN THK	
			BODY: COPPER (QQ-C-576) TIN PL (MIL-T-10727) TYPE I	
QTY.	DESCRIPTION	PART NO.	MATERIAL & FINISH	
UNLESS OTHERWISE SPECIFIED DIM. ARE IN INCHES. TOLERANCES ON: DECIMALS ±.003 ANGLES ±5°		CONTRACT NO. —#—	AMP INCORPORATED HARRISBURG, PENNSYLVANIA	
MATERIAL SEE TABLE I		DR <i>H.C. Youngblood</i> 11-11-66 COP <i>D. Swabell</i> 11-15-66 APPD <i>D. Swabell</i> 11-16-66	NAME WIRE TERMINAL COPALUM-STRANDED/SOLID WIRE SIZE: #6	
HEAT TREAT —#—		DSGN APPD	SIZE B	CODE IDENT NO. 00779
FINISH SEE TABLE I		OTHER APPD	NUMBER 50719	
SCALE 4:1		WT	CALC #	ACTUAL #
			SHEET 1 OF 1	

CUSTOMER DRAWING