

© 1966 BY AMP INCORPORATED. ALL RIGHTS RESERVED. AMP PRODUCTS ARE COVERED BY PATENTS AND/OR PATENT PENDING.


Unauthorized reproduction or use of this drawing without written permission of AMP INCORPORATED is prohibited.

NUMBER 50719

S

C

B



TONGUE MATERIAL THK = .048 ±.003

50719-6	1.504	.679	.515 ±.005	1/2	OBSELETE
50719-5	1.415	.500	.445 ±.003	6	OBSELETE
50719-4			.453 ±.005	7/16	OBSELETE
50719-3	1.504	.679	.390 ±.005	3/8	
50719-2			.328 ±.005	5/16	
50719-1	1.415	.500	.265 ±.005	1/4	
50719			.197 ±.005	10	
PART NO.	"A"	"B"	"C"	"D"	

AMP 1470-1 (11/64) 5

REVISIONS				
ZONE	LTR	DESCRIPTION	DATE	APPROVED
	O	PER NPS. 66-1760-1764	11-15-66	ST
	A	REMOVED ENGRG CONT PER REV NPS 66-1760-1764	7/10/67	RHW
	B	REV TITLE PER ECN PC-5545	12-6-68	RHW
	C	ADDED 50719-5 NPS 69-0554	12-16-69	Jwa
	D	ADDED 50719-6 NPS 75-1756	6-17-75	Jwa
	E	REVISED PER G-1651	11/8/85	pm
	F	OBSELETE - 4 #6 G-2508	7/23/87	pm
	G	OBSELETE - 5 PER S-2856	8/3/88	W.S.V.

TABLE I

1	WIRE TERMINAL	SEE TABLE II	INSERT: BRASS (MIL-C-50) TIN PL (MIL-T-10727) TYPE I .0003 MIN THK	
			BODY: COPPER (QQ-C-576) TIN PL (MIL-T-10727) TYPE I	
QTY.	DESCRIPTION	PART NO.	MATERIAL & FINISH	
UNLESS OTHERWISE SPECIFIED DIM. ARE IN INCHES. TOLERANCES ON: DECIMALS ±.003 ANGLES ±5°		CONTRACT NO. —H—	AMP INCORPORATED HARRISBURG, PENNSYLVANIA	
MATERIAL		DR <i>A.C. Young</i> 11-11-66	NAME WIRE TERMINAL	
SEE TABLE I		CD <i>D. Swabell</i> 11-15-66	COPALUM-STRANDED/SOLID	
HEAT TREAT —H—		APPD <i>D. Swabell</i> 11-16-66	WIRE SIZE: #6	
FINISH SEE TABLE I		DSGN APPD	SIZE B	CODE IDENT NO. 00779
		OTHER APPD	NUMBER 50719	WT CALC ACTUAL —H—
			SCALE 4:1	SHEET 1 OF 1

AMP INFO
LOC 686

CUSTOMER DRAWING