




6	98.65 [3.884]	96.52 [3.800]	39	40	9-146461-0
6	101.19 [3.984]	99.06 [3.900]	38	39	8-146461-9
6	96.11 [3.784]	93.98 [3.700]	37	38	8-146461-8
6	93.57 [3.684]	91.44 [3.600]	36	37	8-146461-7
6	91.03 [3.584]	88.90 [3.500]	35	36	8-146461-6
6	88.49 [3.484]	86.36 [3.400]	34	35	8-146461-5
6	85.95 [3.384]	83.82 [3.300]	33	34	8-146461-4
6	83.41 [3.284]	81.28 [3.200]	32	33	8-146461-3
6	80.87 [3.184]	78.74 [3.100]	31	32	8-146461-2
6	78.33 [3.084]	76.20 [3.000]	30	31	8-146461-1
6	75.79 [2.984]	73.66 [2.900]	29	30	8-146461-0
6	73.25 [2.884]	71.12 [2.800]	28	29	7-146461-9
6	70.71 [2.784]	68.58 [2.700]	27	28	7-146461-8
6	68.17 [2.684]	66.04 [2.600]	26	27	7-146461-7
6	65.63 [2.584]	63.50 [2.500]	25	26	7-146461-6
6	63.09 [2.484]	60.96 [2.400]	24	25	7-146461-5
6	60.55 [2.384]	58.42 [2.300]	23	24	7-146461-4
6	58.01 [2.284]	55.88 [2.200]	22	23	7-146461-3
6	55.47 [2.184]	53.34 [2.100]	21	22	7-146461-2
6	52.93 [2.084]	50.80 [2.000]	20	21	7-146461-1
6	50.39 [1.984]	48.26 [1.900]	19	20	7-146461-0
6	47.85 [1.884]	45.72 [1.800]	18	19	6-146461-9
6	45.31 [1.784]	43.18 [1.700]	17	18	6-146461-8
6	42.77 [1.684]	40.64 [1.600]	16	17	6-146461-7
6	40.23 [1.584]	38.10 [1.500]	15	16	6-146461-6
6	37.69 [1.484]	35.56 [1.400]	14	15	6-146461-5
6	35.15 [1.384]	33.02 [1.300]	13	14	6-146461-4
6	32.61 [1.284]	30.48 [1.200]	12	13	6-146461-3
6	30.07 [1.184]	27.94 [1.100]	11	12	6-146461-2
6	27.53 [1.084]	25.40 [1.000]	10	11	6-146461-1
6	24.99 [.984]	22.86 [.900]	9	10	6-146461-0
6	22.45 [.884]	20.32 [.800]	8	9	5-146461-9
6	19.91 [.784]	17.78 [.700]	7	8	5-146461-8
6	17.37 [.684]	15.24 [.600]	6	7	5-146461-7
6	14.83 [.584]	12.70 [.500]	5	6	5-146461-6
6	12.29 [.484]	10.16 [.400]	4	5	5-146461-5
6	9.75 [.384]	7.62 [.300]	3	4	5-146461-4
6	7.21 [.284]	5.08 [.200]	2	3	5-146461-3
6	4.67 [.184]	2.54 [.100]	1	2	5-146461-2
6	2.13 [.084]	-	-	1	5-146461-1
PLATING	G	F	E	NO. OF POSITIONS	PART NUMBER

5	98.65 [3.884]	96.52 [3.800]	39	40	4-146461-0
5	101.19 [3.984]	99.06 [3.900]	38	39	3-146461-9
5	96.11 [3.784]	93.98 [3.700]	37	38	3-146461-8
5	93.57 [3.684]	91.44 [3.600]	36	37	3-146461-7
5	91.03 [3.584]	88.90 [3.500]	35	36	3-146461-6
5	88.49 [3.484]	86.36 [3.400]	34	35	3-146461-5
5	85.95 [3.384]	83.82 [3.300]	33	34	3-146461-4
5	83.41 [3.284]	81.28 [3.200]	32	33	3-146461-3
5	80.87 [3.184]	78.74 [3.100]	31	32	3-146461-2
5	78.33 [3.084]	76.20 [3.000]	30	31	3-146461-1
5	75.79 [2.984]	73.66 [2.900]	29	30	3-146461-0
5	73.25 [2.884]	71.12 [2.800]	28	29	2-146461-9
5	70.71 [2.784]	68.58 [2.700]	27	28	2-146461-8
5	68.17 [2.684]	66.04 [2.600]	26	27	2-146461-7
5	65.63 [2.584]	63.50 [2.500]	25	26	2-146461-6
5	63.09 [2.484]	60.96 [2.400]	24	25	2-146461-5
5	60.55 [2.384]	58.42 [2.300]	23	24	2-146461-4
5	58.01 [2.284]	55.88 [2.200]	22	23	2-146461-3
5	55.47 [2.184]	53.34 [2.100]	21	22	2-146461-2
5	52.93 [2.084]	50.80 [2.000]	20	21	2-146461-1
5	50.39 [1.984]	48.26 [1.900]	19	20	2-146461-0
5	47.85 [1.884]	45.72 [1.800]	18	19	1-146461-9
5	45.31 [1.784]	43.18 [1.700]	17	18	1-146461-8
5	42.77 [1.684]	40.64 [1.600]	16	17	1-146461-7
5	40.23 [1.584]	38.10 [1.500]	15	16	1-146461-6
5	37.69 [1.484]	35.56 [1.400]	14	15	1-146461-5
5	35.15 [1.384]	33.02 [1.300]	13	14	1-146461-4
5	32.61 [1.284]	30.48 [1.200]	12	13	1-146461-3
5	30.07 [1.184]	27.94 [1.100]	11	12	1-146461-2
5	27.53 [1.084]	25.40 [1.000]	10	11	1-146461-1
5	24.99 [.984]	22.86 [.900]	9	10	1-146461-0
5	22.45 [.884]	20.32 [.800]	8	9	146461-9
5	19.91 [.784]	17.78 [.700]	7	8	146461-8
5	17.37 [.684]	15.24 [.600]	6	7	146461-7
5	14.83 [.584]	12.70 [.500]	5	6	146461-6
5	12.29 [.484]	10.16 [.400]	4	5	146461-5
5	9.75 [.384]	7.62 [.300]	3	4	146461-4
5	7.21 [.284]	5.08 [.200]	2	3	146461-3
5	4.67 [.184]	2.54 [.100]	1	2	146461-2
5	2.13 [.084]	-	-	1	146461-1
PLATING	G	F	E	NO. OF POSITIONS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DATE	1/17/96		 TE Connectivity
		DRAWN BY	J. HOFFMAN		
		CHECKED BY	G. DUBNICZKI		
		APPROVED BY	G. DUBNICZKI		
		DATE	3/18/96		
DIMENSIONS: mm [INCHES]		TO FRANCES UNLESS OTHERWISE SPECIFIED: 0 P.L.C. ± — 1 P.L.C. ± — 2 P.L.C. ± 0.51[.02] 3 P.L.C. ± 0.127[.005] 4 P.L.C. ± 0.0127[.0005] ANGLES ± = — FINISH		NAME HEADER ASSEMBLY, MOD II, STACKING, SINGLE ROW, .025 S.POST, UNSHROUDED	
MATERIAL 		WEIGHT —		SIZE A1	
SEE TABLE		CUSTOMER DRAWING		CAGE CODE 00779	
				DRAWING NO. 146461	
				RESTRICTED TO —	
				SCALE 4:1	
				SHEET 1 OF 1	
				REV B	