







LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	OWN
AD	00	0		RELEASED PER EC 0512-0317-04	22NOV04	BM


- 1 HOUSING MATERIAL: LIQUID CRYSTAL POLYMER
COLOR: NATURAL.
- 2 CONTACT MATERIAL: PHOSPHOR BRONZE
- 3 CONTACT FINISH:(B)
UNDERPLATE (ENTIRE CONTACT):
0.00127 MIN NICKEL PER SAE-AMS-QQ-N-290
ON MATING SURFACES:
CONFORMS TO ALL TESTING SPECIFIED FOR TELCORDIA
UNCONTROLLED ENVIRONMENT.
ON LEADS:
0.0006 MIN MATTE TIN PER ASTM B 545 OVER UNDERPLATE.
LUBRICATION (MIN MATING SURFACES):
SURFACE CONDITIONER AFTER PLATING.

- 4 PART MARKING LOCATED APPROXIMATELY AS SHOWN.
- 5 DIMENSION APPLIES WHEN SEATED ON PRINTED CIRCUIT BOARD.



$\phi 0.725 \pm 0.075$
 $\phi 0.15$ TYP
PLATED THROUGH HOLE

RECOMMENDED CIRCUIT PATTERN
(COMPONENT SIDE)



DETAIL Z
SCALE 20:1

94	47	95.88	240	5223011-8
46	23	47.88	120	5223011-4
22	11	23.88	60	5223011-2
10	5	11.88	30	5223011-1
C	B	A	NO OF SIGNAL POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN B MCMASTER	22NOV04	Tyco Electronics Corporation	
DIMENSIONS:		CHK R WERTZ	22NOV04	Harriaburg, Pa 17105-3608	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD R WERTZ	22NOV04	NAME	
mm		PRODUCT SPEC		ASSEMBLY, PIN, SIGNAL, VERTICAL, Z-PACK 2mm FB, 5 ROW, PRESS FIT	
0 PLC ± -		APPLICATION SPEC		5mm MATING POST W/ 4.25mm PRESS FIT LEADS	
1 PLC ± -		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
2 PLC ± 0.13		WEIGHT		A1 00779	
3 PLC ± -		CUSTOMER DRAWING			
4 PLC ± -		SCALE 4:1 SHEET 1 OF 1 REV Q			
ANGLES					
FINISH					