


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
CE	—		B	REV; ECO-10-025423	15DEC10	JB	DK

1. DIMENSIONS IN [] ARE IN INCHES
2. MAXIMUM INSERTION LOSS IS 0.5dB PLUS CABLE ATTENUATION OF 0.7dB/km AT 1310nm (SEE TABLE)
3. 50 dB MIN RETURN LOSS
4. PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TYCO ELECTRONICS STANDARD 230-702



0.50	12.00±0.15 [472.4±6.0]	1-5492020-2
0.60	144.78±0.61 [5700±24]	1-5492020-1
0.51	25±0.3 [984±12]	1-5492020-0
0.50	9±0.15 [354±6]	5492020-9
0.50	7±0.08 [276±3]	5492020-8
0.51	20±0.3 [787±12]	5492020-7
0.50	15±0.15 [591±6]	5492020-6
0.50	10±0.15 [394±6]	5492020-5
0.50	5±0.08 [197±3]	5492020-4
0.50	3±0.05 [118±2]	5492020-3
0.50	2±0.05 [79±2]	5492020-2
0.50	1±0.05 [39±2]	5492020-1
2. MAX IL (dB)	L METERS [INCHES]	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
C.S.VASU
02 JAN 06

CHK
J.DUNCAN
02 JAN 06

APVD
J.DUNCAN
02 JAN 06

Tyco Electronics

Tyco Electronics Corporation
Harrisburg, Pa 17105-3608

DIMENSIONS:
METERS[INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

MATERIAL -

FINISH -

NAME
CABLE ASSEMBLY, FIBER OPTIC, SINGLEMODE LDD, AMP SC DUPLEX (NG) TO 2.5mm BAYONET, OPTIMATE

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=5492020

RESTRICTED TO
-

WEIGHT -

SCALE
NTS

SHEET
1 OF 1

REV
B

CUSTOMER DRAWING

SCALE
NTS

SHEET
1 OF 1

REV
B