


LOC	DIST	REVISIONS				
CE	16	P	LTR	DESCRIPTION	DATE	APVD
			B	REVISED PER ECR-08-003988	05MAR08	JWD JD

1. MAXIMUM INSERTION LOSS IS 0.2dB PLUS CABLE
ATTENUATION OF 0.7dB/km AT 1310nm. (SEE TABLE)
2. MINIMUM RETURN LOSS: 55 dB
3. CONNECTOR END FACE TO MEET LC
GEOMETRY REQUIREMENTS.
4. PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF
TYCO ELECTRONICS STANDARD 230-702.



0.21	10.00±0.15 [393.70±6.0]	1-6374518-0
0.20	5.00±0.08 [196.90±3.00]	6374518-5
0.20	4.00±0.08 [157.50±3.00]	6374518-4
0.20	3.00±0.05 [118.10±2.00]	6374518-3
0.20	2.00±0.05 [78.70±2.00]	6374518-2
0.20	1.00±0.05 [39.40±2.00]	6374518-1
MAX IL (dB)	L METERS [INCHES]	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN KATHY HE	28SEP05	Tyco Electronics Corporation Harrisburg Pa, 17105-3608		
		CHK RICHARD ZHAO	28SEP05			
DIMENSIONS: METERS [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD J.DUNCAN	28SEP05	NAME CABLE ASSY, FIBER OPTIC, 900 BUFFER, SM LC TO LC, OPTIMATE		
		PRODUCT SPEC				
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -	APPLICATION SPEC		SIZE A3	CAGE CODE 00779	DRAWING NO C-6374518
		WEIGHT	-			
MATERIAL -	FINISH -	CUSTOMER DRAWING		SCALE NTS	SHEET 1 OF 1	REV B