





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	Y3	REVISED PER ECR-15-014064	03MAR2016	NK	NL

- 1 POST TO WITHSTAND 13 NEWTONS [3 LBS.] MIN. AXIAL FORCE IN BOTH DIRECTIONS SHOWN WITHOUT DISLODGING.
- 2 TOLERANCES APPLY TO SOLDER SIDE OF BOARD.
- 3 MEASURED AT SURFACE -A-
- 4 PLASTIC FLASH PERMITTED IN THIS AREA.
- 5 PARTS COMPLY WITH SOLDERABILITY SPEC. 109-11-2.
- 6 ONE HOLE MAY BE UNDERSIZED 0.81-0.89 [.032-.035] DIA. FOR ASSEMBLY RETENTION DURING WAVE SOLDERING.
- 7 MATERIAL: HEADER-THERMOPLASTIC POLYESTER UL94V-0 (NATURAL)
POST-COPPER ALLOY (TIN-PLATED)
- 8 COORDINATE DIMENSION APPLIES FROM CENTER OF ACTUAL FEATURE.
- 9 PLASTIC BURRS CAUSED BY CUT-OFF TOOLING ARE PERMITTED WITHIN THE MAXIMUM TOLERANCE ENVELOPE.
- 10 POSTS TO BE MEASURED WHEN STRIP IS HELD FLAT.
- 11 POSTS MUST WITHSTAND TWO 90° BENDS AGAINST EXTRUSION WITHOUT BREAKING.
- 12 DIMENSION SHOULD BE 3.30 [.130] WHEN MATING WITH A MTA-100 CONNECTOR ASSEMBLY OR A CST-100 CONNECTOR.
- 13 PIN BURR OF 0.13 [.005] MAX. VERTICAL AND 0.08 [.003] MAX. HORIZONTAL PERMITTED AT POST TIPS ON BOTH ENDS.

71.12	2,800	28	2-640454-8
68.58	2,700	27	2-640454-7
66.04	2,600	26	2-640454-6
63.50	2,500	25	2-640454-5
60.96	2,400	24	2-640454-4
58.42	2,300	23	2-640454-3
55.88	2,200	22	2-640454-2
53.34	2,100	21	2-640454-1
50.80	2,000	20	2-640454-0
48.26	1,900	19	1-640454-9
45.72	1,800	18	1-640454-8
43.18	1,700	17	1-640454-7
40.64	1,600	16	1-640454-6
38.10	1,500	15	1-640454-5
35.56	1,400	14	1-640454-4
33.02	1,300	13	1-640454-3
30.48	1,200	12	1-640454-2
27.94	1,100	11	1-640454-1
25.40	1,000	10	1-640454-0
22.86	.900	9	640454-9
20.32	.800	8	640454-8
17.78	.700	7	640454-7
15.24	.600	6	640454-6
12.70	.500	5	640454-5
10.16	.400	4	640454-4
7.62	.300	3	640454-3
5.08	.200	2	640454-2
MM	[IN]	NO OF POSITIONS	PART NUMBER
L			

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN S. HAMM 09-NOV-2001		 TE Connectivity	
DIMENSIONS: mm [INCHES]				CHK D. BOSSI 09-NOV-2001			
TOLERANCES UNLESS OTHERWISE SPECIFIED:				APVD D. BOSSI 09-NOV-2001		NAME	
				PRODUCT SPEC		MTA-100 HDR ASSY, POLARIZED, NOTCHED, .025 SQUARE STRAIGHT POST, TIN PLATED	
				APPLICATION SPEC			
MATERIAL				WEIGHT		SIZE	
FINISH				CUSTOMER DRAWING		CAGE CODE	
7				A1		DRAWING NO	
7				SCALE		REV	
7				8:1		SHEET	
7				1		OF	
7				REV		Y3	