

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

LOC

DY

DIST

-

P

LTR

DESCRIPTION

E3

ECR-14-010370

DATE

10JUL14

DWN

I.T

APVD

W.H

Notes:

1

CUTOUT FEATURE AVAILABLE ONLY ON 5H ASSY P/N -1 (40P) AND -2 (60P).

2

0.00038 MIN GOLD PLATING (15u INCHES GOLD PLATING)

3

CONNECTOR DIMENSIONS REFERENCED FROM DRAWING WHICH CONN. P/Ns BASED

0.00076 MIN GOLD PLATING (30u INCHES GOLD PLATING)

450								61.8	88	84.4	42.2	140	1-	-6	7-	-6
								53.8				120	1-	-5	7-	-5
								45.8	72	68.4	34.2	100	1-	-4	7-	-4
								37.8	56	52.4	26.2	80	1-	-3	7-	-3
								29.8	44	40.4	20.2	60	1-	-2	7-	-2
700	7H	12			6.85	7.25		21.8	32	28.4	14.2	40	1-5179030-1		7-5177986-1	
								69.8				160		-8	6-	-8
								61.8	88	84.4	42.2	140		-6	6-	-6
								53.8				120		-5	6-	-5
550								45.8	72	68.4	34.2	100		-4	6-	-4
								37.8	56	52.4	26.2	80		-3	6-	-3
								29.8	44	40.4	20.2	60		-2	6-	-2
800	6H	12			5.85	6.25		21.8	32	28.4	14.2	40	5084615-1		6-5177986-1	
								85.8	104	100.4	50.2	200	1-	-0	5-	-0
								69.8				160		-8	5-	-8
								61.8	88	84.4	42.2	140		-6	5-	-6
								53.8				120		-5	5-	-5
								45.8	72	68.4	34.2	100		-4	5-	-4
								37.8	56	52.4	26.2	80		-3	5-	-3
								29.8	44	40.4	20.2	60		-2	5-	-2
900	5H	12	12	17	4.85	5.25		21.8	32	28.4	14.2	40	5084614-1		5-5177986-1	

0.0002 MIN GOLD PLATING (7.8u INCHES GOLD PLATING)

450	7H	12	16	17	6.85	7.25		53.8	72	68.4	34.2	120	3-5179030-5		4-5177986-5	
								85.8				200	1-	-0	4-	-0
								77.8	104	100.4	50.2	180		-9	3-	-9
								69.8				160		-8	3-	-8
								61.8	88	84.4	42.2	140		-6	3-	-6
								53.8				120		-5	3-	-5
400								45.8	72	68.4	34.2	100		-4	3-	-4
								37.8	56	52.4	26.2	80		-3	3-	-3
								29.8	44	40.4	20.2	60		-2	3-	-2
600	8H	12			7.85	8.25		21.8	32	28.4	14.2	40	5179031-1		3-5177986-1	
								85.8				200	1-	-0	3-	-0
								77.8	104	100.4	50.2	180		-9	2-	-9
								69.8				160		-8	2-	-8
								61.8	88	84.4	42.2	140		-6	2-	-6
								53.8				120		-5	2-	-5
450								45.8	72	68.4	34.2	100		-4	2-	-4
								37.8	56	52.4	26.2	80		-3	2-	-3
								29.8	44	40.4	20.2	60		-2	2-	-2
700	7H	12			6.85	7.25		21.8	32	28.4	14.2	40	5179030-1		2-5177986-1	
								61.8	88	84.4	42.2	140		-6	1-	-6
								53.8				120		-5	1-	-5
550								45.8	72	68.4	34.2	100		-4	1-	-4
								37.8	56	52.4	26.2	80		-3	1-	-3
								29.8	44	40.4	20.2	60		-2	1-	-2
800	6H	12			5.85	6.25		21.8	32	28.4	14.2	40	5179029-1		1-5177986-1	
								69.8				160		-8		-8
								61.8	88	84.4	42.2	140		-6		-6
								53.8				120		-5		-5
								45.8	72	68.4	34.2	100		-4		-4
								37.8	56	52.4	26.2	80		-3		-3
								29.8	44	40.4	20.2	60		-2		-2
900	5H	12	12	17	4.85	5.25		21.8	32	28.4	14.2	40	5177984-1		5177986-1	

DETAIL B

LOCATION BOSS

DETAIL B

WINDING THE COVER TAPE AROUND THE OUTER PERIPHERY IN A TURN.

10 HOLES

300mm WITHOUT CHARGE APPROX

300mm WITHOUT CHARGE APPROX

WITH PRODUCT CHARGE

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN FLORENCE TAN 30AUG04

CHK ERIC TNG 30MAY2012

APVD SE LEONG 30MAY2012

PRODUCT SPEC 108-5390

APPLICATION SPEC 114-5254

WEIGHT -

CUSTOMER DRAWING

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±0.3

1 PLC ±0.3

2 PLC ±0.25

3 PLC ±0.2

4 PLC ±0.2

ANGLES ±3°

MATERIAL -

FINISH -

NAME PLUG ASSEMBLY (0.5 BOSS LENGTH) FOR FH 0.8 B-T-B CONN. ON TAPING

SIZE A3

CAGE CODE 00779

DRAWING NO C-5177986

RESTRICTED TO -

SCALE 2:1

SHEET 1 OF 1

REV E3