





P	LTR	DESCRIPTION	DATE	DWN	APVD
	D	REVISED PER 0G3B-1115-04	23JUNE05	KW	DC
	D1	REVISED PER ECO-09-023313	09OCT09	KK	AEG



1. WIRE RANGE: 0.30–0.87mm² (22–18 AWG).
2. INSULATION RANGE: 1.50–2.40 DIA.
- 3 FINISH: 0.76μm MINIMUM GOLD OVER 1.27μm MINIMUM NICKEL REQUIRED
- 4 FINISH: NICKEL BASE PLATE ON ALL SURFACES IN THIS AREA.
- 5 FINISH: 2.54μm MINIMUM TIN-LEAD ON ALL SURFACES IN THIS AREA.
- 6 FINISH: 2.54μm MINIMUM TIN ON ALL SURFACES IN THIS AREA.
- 7 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



SECTION B-B
SCALE 20:1



SECTION A-A
SCALE 20:1

METRIC

	3 4 6	0.22[.009] PHOS BRONZE	794576-4
7 SUPERCEDED	3 4 5	0.22[.009] PHOS BRONZE	794576-2
	PRE-TIN	0.22[.009] PHOS BRONZE	794576-1
	FINISH	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. HOOVER 07-FEB-2003		Tyco Electronics Corporation Harrisburg, Pa 17105-3608	
DIMENSIONS: mm [INCHES]		CHK D. COLEY 07-FEB-2003		NAME	
		APVD D. COLEY 07-FEB-2003		CONTACT, MALE, AMP-DUAC(TM)	
		PRODUCT SPEC			
		APPLICATION SPEC			
MATERIAL 0.22 [.009]PH BRZ		WEIGHT		SIZE A2	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 0.10 [.004] 3 PLC ± 4 PLC ± ANGLES ± FINISH SEE TABLE		108-1646 114-6067		CAGE CODE 00779	
		CUSTOMER DRAWING		DRAWING NO C=794576	
				RESTRICTED TO -	
				SCALE 14:1 SHEET 1 OF 1 REV D1	