



## E7012PC004 Product Details

[Share](#) [Print](#) [Email](#)


**E7012PC004**  
(1423169-8)

TE Internal Number: 1423169-8

 [Active](#)

### Time Delay Relays

[Not EU RoHS or ELV Compliant](#)

#### Product Highlights:

- 7000 Electropneumatic Timing - Nuclear Qualified Series
- Input Voltage = 125 VDC
- Contact - Arrangement = 2 Form C, DPDT, 2 C/O
- Contact Rating = 1A @ 125 VDC
- Mounting Options = Mounting Holes, Panel Mount

[View all Features](#)

### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

### Documentation & Additional Information

#### Product Drawings:

- None Available

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- [Nuclear E7000 Series 2-Pole Timing Relay](#) (PDF, English)

#### CAD Files:

- None Available

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- Series = 7000 Electropneumatic Timing - Nuclear Qualified
- Termination Type = Screw Terminal

#### Electrical Characteristics:

- Input Voltage (VDC) = 125
- Contact Rating = 1A @ 125 VDC

#### Contact Features:

- Mounting Options = Mounting Holes, Panel Mount
- Mode of Operation = On-Delay
- Delay Time = 1.5 seconds to 15 seconds
- Type of Control = Knob
- Repeatability, Max. = ± 10%
- Approx. Dimensions (L x W x H) (mm [in]) = 82.55 x 78.49 x 107.95 [3.252 x 3.092 x 4.253]

#### Configuration Features:

- [Contact - Arrangement](#) = 2 Form C, DPDT, 2 C/O
- Multiple Timing Ranges = Without

#### Industry Standards:

- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process

#### Conditions for Usage:

- Temperature Range (°C) = 21 - 40

#### Other:

- Brand = Agastat

### Corporate Information

[Who We Are](#)

[Investors](#)

[News Room](#)

[Supplier Portal](#)

[Careers](#)

### Quick Links

[Check Distributor Inventory](#)

[Cross Reference](#)

[Find Documents & Drawings](#)

[Product Compliance Support Center](#)

[Site Map](#)

### Customer Support

[Email or Chat With Us](#)

[Find a Phone Number](#)

[Search Knowledge Base](#)

[Manage your Account](#)

### Keep Me Informed

Receive TE News, Events & Technology Updates

