

REVISIONS

| P | LTR | DESCRIPTION                   | DATE      | DWN | APVD |
|---|-----|-------------------------------|-----------|-----|------|
|   | A1  | Released as per ECR-08-022292 | 4-Sep-08  | SP  | JC   |
|   | V   | ECR-16-003733                 | 12MAR2016 | KR  | TN   |
|   |     |                               |           |     |      |
|   |     |                               |           |     |      |


LASER MARKING: TE LOGO PN VALUE  
TOLERANCE & DATE CODE

M6 ST/STEEL TERMINAL STUDS.  
EACH SUPPLIED WITH:-  
2 OFF M6 ST/STEEL FULL NUTS  
2 OFF M6/STEEL PLAN WASHERS

- 1 FOR FURTHER INFORMATION SEE DATA SHEET FOR  
HS SERIES-ALUMINIUM HOUSED RESISTORS
- 2 FOR A SPECIFIC PN FOR A RESISTANCE VALUE  
AND TOLERANCE, PLEASE REFER TO DMF

GOLD ANODISED  
ALUMINIUM HOUSINGS

RoHS Compliant



SCALE 1:2

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 28.SEP.05

CHK DAVE KENNEDY 29.SEP.05

J CATCHPOLE 29.SEP.05

APVD J CATCHPOLE

PRODUCT SPEC

-

APPLICATION SPEC

-


WEIGHT

-

CUSTOMER DRAWING

DIMENSIONS:

mm



TOLERANCES UNLESS  
OTHERWISE SPECIFIED:

0 PLC ±0.5  
1 PLC ±0.2  
2 PLC ±0.1  
3 PLC ±  
4 PLC ±  
ANGLES ±5°

MATERIAL

material\_2

FINISH

finish\_spec\_2



TE Connectivity

NAME

HSC250 ALUMINIUM HOUSED  
POWER RESISTOR

SIZE

A3

CAGE CODE

00779

DRAWING NO

C=1630024

RESTRICTED TO

-

SCALE 1:1

SHEET 1 OF 1

REV V