



+ RELAYS, CONTACTORS & SWITCHES

TIME DELAY RELAYS



✓ Active

TE CONNECTIVITY (TE)

E7014OB004="RLY,NUC,ON,4P,24VD

Agastat | 7000 Electropneumatic Timing - Nuclear Qualified

E7014OB004

TE Internal Number: 1423173-1

Not EU RoHS Compliant

Not EU ELV Compliant

Type of Control Knob

Input Voltage (VDC) 24

Timing Range (Off-Time) (seconds) .7 – 7

Mode of Operation On-Delay

Delay Time .7 – 7 seconds

DOCUMENTATION

Catalog Pages/Data Sheets

5-1773450-5_sec12_E7000

PDF

English

Instruction Sheets

Instruction Sheet (U.S.)

Nuclear E7000 Series 4-Pole Timing Relay

PDF

English

FEATURES

Please review product documents or [contact us](#) for the latest agency approval information.

Product Type Features

Product Category Electromechanical Relays

Relay Type Time Delay

Product Type Relay

Configuration Features

Multiple Timing Ranges Without

Electrical Characteristics

Input Voltage (VDC) 24

Timing Range (Off-Time) (seconds) .7 – 7

Actuating System DC

Contact Features

Type of Control Knob

Delay Time .7 – 7 seconds

Contact Arrangement 4 Form C, 4PDT, 4 C/O

Termination Features

Termination Type Screw Terminals

Mechanical Attachment

Mounting Type Mounting Holes, Panel Mount

Dimensions

Dimensions (L x W x H) (Approximate) 114.8 x 65.3 x 78.5 mm [4.52 x 2.57 x 3.09 in]

Usage Conditions

Operating Temperature Range (°C) 21 – 40

Operation/Application

Mode of Operation On-Delay

Other

Repeatability (Max) ±10%

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

PDF
