

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

© COPYRIGHT - By TE Connectivity

LOC
HBDIST
—

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
A		CHANGE DATE&TE LOGO ECO-08-007869	16-APR-08	CY.ZBH.Y	
B		1.CHANGE LOGO2.ADD LINE IDENTIFICATIONS.TERMINALS TOLERANCE CLARIFICATION ECO-12-005305	26-MAR-12	YS.H	BH.Y








Diagram dimension	Tolerance
max. 1mm	±0.1mm
1 - 3mm	±0.2mm
min. 3mm	±0.3mm

DRILLING DIAGRAM
BOTTOM VIEW (2/1)CONNECTION DIAGRAM
BOTTOM VIEW (2/1)

NOTE

① 1.LOT NO. SYSTEM AS FOLLOWING:

WEEK
YEAR

② 2.TERMINAL DIMENSIONS BEFORE SOLDER DIP

③ 3.FOR THE TIN-PLATING OF THE PINS: +0.1mm FOR WIDTH, THICKNESS AND DIAMETER
+0.5mm FOR LENGTH

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC	± -
1 PLC	± -
2 PLC	± -
3 PLC	± -
4 PLC	± -
ANGLES	± -
MATERIAL	FINISH
-	-

DWN K.Okada	CHK H.Sasaki	APVD A.Nagai
PRODUCT SPEC	APPLICATION SPEC	WEIGHT
-	-	-
CUSTOMER DRAWING	SCALE 4:1	SHEET 1 of 2



TE Connectivity

NAME

SDT-LMR2 CUSTOMER DRAWING

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C=1461100

-

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

- , - .

© COPYRIGHT - By TE Connectivity

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

HB

-

P

LTR

DESCRIPTION

DATE

DWN

APVD

-

SEE SHEET 1

-

-

-

	SDT-S-124LMR2	2-1440009-6	108-79452	STANDARD	f
⑩	SDT-S-112LMR2	1440003	108-79451	STANDARD	e
	SDT-S-109LMR2	9-1419125-5	108-79450	STANDARD	d
⑨	SDT-S-106LMR2	5-1440007-0	108-79449	STANDARD	c
	SDT-S-105LMR2	8-1419125-3	108-79448	STANDARD	b
⑧	SDT-S-103LMR2	1461100-1	108-79447	STANDARD	a
	DESCRIPTION	TE PART NO	PRODUCT SPEC	DESCRIPTION	No.

RELAY TYPE

		EPOXY RESIN	SEAL (BASE & TERMINAL)	15
		EPOXY RESIN	SEAL (BASE & YOKE)	14
		3UEW	MAGNETIC WIRE	13
94V-0		P.B.T	CASE	12
94V-0		P.B.T	BOBBIN	11
	SOLDER DIP	C.P WIRE	COIL TERMINAL	10
94V-0		NYRON	CARD	9
		AgSnO	MOVABLE CONTACT	8
		AgSnO	NO.CONTACT	7
		STEEL	HINGE SPRING	6
	SOLDER DIP	Cu ALLOY	NO.TERMINAL	5
	SOLDER DIP	Cu ALLOY	MOVABLE SPRING	4
	NIP	STEEL	CORE	3
	NIP	STEEL	ARMATURE	2
	NIP	STEEL	YOKE	1
INCOMBUSTIBILITY	TREATMENT	MATERIAL	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

K.Okada

CHK

H.Sasaki

APVD

A.Nagai

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

-

CUSTOMER DRAWING



TE Connectivity

NAME

SDT-LMR2 CUSTOMER DRAWING

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C=1461100

-


SCALE 4:1

SHEET 2 of 2

REV B

DIMENSIONS:

mm



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± -
1 PLC	± -
2 PLC	± -
3 PLC	± -
4 PLC	± -
ANGLES	± -

MATERIAL

-

FINISH

-