




Raychem
PART NO.
MTC100-JA2-S11-T14
DATE CODE

ZONE	DATE	DESCRIPTION	DATE	APPROVED
B	7-20-94	REVISED PER ECN T-19483	7-20-94	R.J.

△ WEIGHT (MAX.): $\frac{\text{LBS}}{.0109} \mid \frac{\text{GRAMS}}{4.94}$

△ SOCKET ONE: SOCKET NUMBER ONE MARKED IN CONTRASTING COLOR.

3. WAFER: WAFER MEETS THE REQUIREMENTS OF RAYCHEM SPECIFICATION D-6012.

2. FINISH: 2-A SOCKET WAFER; FINISH TO BE AS MOLDED.
2-B SOCKET CONTACT; GOLD PLATE PER MIL-G-45204 CLASS I.
(ENGAGING END)
2-C CONTACT TAIL; COATED WITH SOLDER PER QQ-S-571.

1. MATERIAL: 1-A SOCKET WAFER; HIGH GRADE POLYARYLENE THERMO-PLASTIC.
1-B SOCKET CONTACT; COPPER ALLOY PER QQ-B-750 (A).
1-C SOLDERPAK® REFER TO RAYCHEM DWG. CTA-0036
TERMINATORS ASSY; FOR DATA.

NOTES

If this document is printed it becomes uncontrolled.
Check with the web for latest revision.

SPECIFICATION CONTROL DRAWING

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES BRACKETED DIMENSIONS () ARE METRIC AND TOLERANCES ARE: .XXX: ± .005 (0.13 M.M.) .XX: ± .02 (0.51 M.M.) Δ: ± —	DRAWN	W.V.J.	1-15-81	Raychem RAYCHEM CORPORATION 3300 LANTANA DRIVE, SUITE 100 MILFORD, MA 01801-1001	
	CHECKED				
	APPROVED			TITLE KIT, 2" SOCKET WAFER "A" WITH SOLDERPAK® TERMINATORS, FOR ROUND WIRE (20-26 AWG), 125 °C TEMPERATURE RATING MTC 100 SERIES	
	APPROVED				
	APPROVED				
	SIZE	CODE IDENT	DWG. NO.		
	A	NO. 06090	MTC100-JA2-S11-T14		
DO NOT SCALE THIS DRAWING				WEIGHT △	SHEET 1 OF 1