- **Single Chip With Easy Interface Between UART and Serial-Port Connector of an External Modem or Other Computer Peripheral**
- **Five Drivers and Three Receivers Meet or Exceed the Requirements of ANSI Standard TIA/EIA-232-F and ITU Recommendation V.28 Standards**
- **Supports Data Rates up to 120 kbit/s**
- **Complement to the GD75232**
- **Provides Pin-to-Pin Replacement for the Goldstar GD75323**
- **Pin-Out Compatible With SN75196**
- **Functional Replacement for the MC145405**

DW OR N PACKAGE
(TOP VIEW)



description

The GD75323 combines five drivers and three receivers from the trade-standard SN75188 and SN75189 bipolar quadruple drivers and receivers, respectively. The flow-through design of the GD75323 decreases the part count, reduces the board space required, and allows easy interconnection of the UART and serial-port connector. The all-bipolar circuits and processing of the GD75323 provide a rugged, low-cost solution for this function.

The GD75323 complies with the requirements of the ANSI TIA/EIA-232-F and ITU (formerly CCITT) V.28 standards. These standards are for data interchange between a host computer and a peripheral at signal rates up to 20 kbit/s. The switching speeds of the GD75323 are fast enough to support rates up to 120 kbit/s with lower capacitive loads (shorter cables). Interoperability at the higher signaling rates cannot be assured unless the designer has design control of the cable and the interface circuits at both ends. For interoperability at signaling rates up to 120 kbit/s, use of ANSI Standard TIA/EIA-423-B and TIA/EIA-422-B and ITU Recommendations V.10 and V.11 are recommended.

The GD75323 is characterized for operation over a temperature range of 0°C to 70°C.

Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

PRODUCTION DATA information is current as of publication date. Products conform to specifications per the terms of Texas Instruments standard warranty. Production processing does not necessarily include testing of all parameters.

Copyright © 1999, Texas Instruments Incorporated

logic symbol†



† This symbol is in accordance with ANSI/IEEE Std 91-1984 and IEC Publication 617-12.

logic diagram (positive logic)



schematic (each driver)



Resistor values shown are nominal.

schematic (each receiver)



Resistor values shown are nominal.

absolute maximum ratings over operating free-air temperature range (unless otherwise noted)†

Supply voltage, V_{CC} (see Note 1) . . . . . 10 V
Supply voltage, V_{DD} (see Note 1) . . . . . 15 V
Supply voltage, V_{SS} (see Note 1) . . . . . –15 V
Input voltage range, V_I: Driver . . . . . –15 V to 7 V
Receiver . . . . . –30 V to 30 V
Output voltage range, V_O (Driver) . . . . . – 15 V to 15 V
Low-level output current, I_{OL} (Receiver) . . . . . 20 mA
Package thermal impedance, θ_{JA} (see Note 2): DW package . . . . . 97°C/W
N package . . . . . 67°C/W
Lead temperature 1,6 mm (1/16 inch) from case for 10 seconds . . . . . 260°C
Storage temperature range, T_{stg} . . . . . – 65°C to 150°C

† Stresses beyond those listed under “absolute maximum ratings” may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under “recommended operating conditions” is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

NOTES: 1. All voltages are with respect to the network ground terminal.
2. The package thermal impedance is calculated in accordance with JESD 51, except for through-hole packages, which use a trace length of zero.

recommended operating conditions

		MIN	NOM	MAX	UNIT
Supply voltage	V_{DD}	7.5	9	13.5	V
	V_{SS}	–7.5	–9	–13.5	
	V_{CC}	4.5	5	5.5	
High-level input voltage, V_{IH}	Driver	1.9			V
Low-level input voltage, V_{IL}	Driver			0.8	V
High-level output current, I_{OH}	Driver			–6	mA
	Receiver			–0.5	
High-level output current, I_{OL}	Driver			6	mA
	Receiver			16	
Operating free-air temperature, T_A		0		70	°C

supply currents over operating free-air temperature range

PARAMETER		TEST CONDITIONS				MIN	MAX	UNIT
I_{DD}	Supply current from V_{DD}	All inputs at 1.9 V,	No load	V_{DD} = 9 V,	V_{SS} = –9 V		25	mA
				V_{DD} = 12 V,	V_{SS} = –12 V		32	
		All inputs at 0.8 V,	No load	V_{DD} = 9 V,	V_{SS} = –9 V		7.5	mA
				V_{DD} = 12 V,	V_{SS} = –12 V		9.5	
I_{SS}	Supply current from V_{SS}	All inputs at 1.9 V,	No load	V_{DD} = 9 V,	V_{SS} = –9 V		–25	mA
				V_{DD} = 12 V,	V_{SS} = –12 V		–32	
		All inputs at 0.8 V,	No load	V_{DD} = 9 V,	V_{SS} = –9 V		–5.3	mA
				V_{DD} = 12 V,	V_{SS} = –12 V		–5.3	
I_{CC}	Supply current from V_{CC}	V_{CC}= 5 V,	All inputs at 5 V,	No load			20	mA

DRIVER SECTION

electrical characteristics over operating free-air temperature range, V_{DD} = 9 V, V_{SS} = –9 V, V_{CC} = 5 V (unless otherwise noted)

PARAMETER		TEST CONDITIONS			MIN	TYP	MAX	UNIT
V_{OH}	High-level output voltage	V_{IL} = 0.8 V,	R_L = 3 kΩ,	See Figure 1	6	7.5		V
V_{OL}	Low-level output voltage (see Note 3)	V_{IH} = 1.9 V,	R_L = 3 kΩ,	See Figure 1		–7.5	–6	V
I_{IH}	High-level input current	V_I = 5 V,	See Figure 2				10	µA
I_{IL}	Low-level input current	V_I = 0,	See Figure 2				–1.6	mA
$I_{OS(H)}$	High-level short-circuit output current (see Note 4)	V_{IL} = 0.8 V,	V_O = 0,	See Figure 1	–4.5	–9	–19.5	mA
$I_{OS(L)}$	Low-level short-circuit output current	V_{IH} = 2 V,	V_O = 0,	See Figure 1	4.5	9	19	mA
r_o	Output resistance (see Note 5)	$V_{CC} = V_{DD} = V_{SS}$ = 0,		V_O = –2 V to 2 V	300			Ω

NOTES: 3. The algebraic convention, where the more positive (less negative) limit is designated as maximum, is used in this data sheet for logic levels only, e.g., if –10 V is maximum, the typical value is a more negative voltage.
4. Output short-circuit conditions must maintain the total power dissipation below absolute maximum ratings.
5. Test conditions are those specified by TIA/EIA-232-F and as listed above.

switching characteristics, V_{DD} = 12 V, V_{SS} = –12 V, V_{CC} = 5 V ±10%, T_A = 25°C

PARAMETER		TEST CONDITIONS		MIN	TYP	MAX	UNIT
t_{PLH}	Propagation delay time, low- to high-level output	R_L = 3 kΩ to 7 kΩ, See Figure 3	C_L = 15 pF,		315	500	ns
t_{PHL}	Propagation delay time, high- to low-level output				75	175	ns
t_{TLH}	Transition time, low- to high-level output	R_L = 3 kΩ to 7 kΩ, See Figure 3	C_L = 15 pF,		60	100	ns
		R_L = 3 kΩ to 7 kΩ, See Figure 3 and Note 6	C_L = 2500 pF,		1.7	2.5	µs
t_{THL}	Transition time, high- to low-level output (see Note 5)	R_L = 3 kΩ to 7 kΩ, See Figure 3	C_L = 15 pF,		40	75	ns
		R_L = 3 kΩ to 7 kΩ, See Figure 3 and Note 7	C_L = 2500 pF,		1.5	2.5	µs

NOTES: 6. Measured between –3-V and 3-V points of the output waveform (TIA/EIA-232-F conditions), all unused inputs are tied either high or low.
7. Measured between 3-V and –3-V points of the output waveform (TIA/EIA-232-F conditions), all unused inputs are tied either high or low.

RECEIVER SECTION

electrical characteristics over recommended operating conditions (unless otherwise noted)

PARAMETER		TEST CONDITIONS		MIN	TYP†	MAX	UNIT
V_{IT+}	Positive-going input threshold voltage	See Figure 5	T_A = 25°C	1.75	1.9	2.3	V
			T_A = 0°C to 70 °C	1.55		2.3	
V_{IT-}	Negative-going input threshold voltage	See Figure 5		0.75	0.97	1.25	
V_{hys}	Input hysteresis voltage ($V_{IT+} - V_{IT-}$)			0.5			
V_{OH}	High-level output voltage	I_{OH} = –0.5 mA	V_{IH} = 0.75 V	2.6	4	5	V
			Inputs open	2.6			
V_{OL}	Low-level output voltage	I_{OL} = 10 mA,	V_I = 3 V		0.2	0.45	V
I_{IH}	High-level input current	V_I = 25 V,	See Figure 5	3.6		8.3	mA
		V_I = 3 V,	See Figure 5	0.43			
I_{IL}	Low-level input current	V_I = –25 V,	See Figure 5	–3.6		–8.3	mA
		V_I = –3 V,	See Figure 5	–0.43			
I_{OS}	Short-circuit output current	See Figure 4			–3.4	–12	mA

† All typical values are at T_A = 25°C, V_{CC} = 5 V, V_{DD} = 9 V, and V_{SS} = –9 V.

switching characteristics, V_{CC} = 5 V, V_{DD} = 12 V, V_{SS} = –12 V, T_A = 25°C

PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
t_{PLH}	Propagation delay time, low- to high-level output	C_L = 50 pF, R_L = 5 kΩ, See Figure 6		107	500	ns
t_{PHL}	Propagation delay time, high- to low-level output			42	150	ns
t_{TLH}	Transition time, low- to high-level output			175	525	ns
t_{THL}	Transition time, high- to low-level output			16	60	ns

PARAMETER MEASUREMENT INFORMATION



Figure 1. Driver Test Circuit for V_{OH}, V_{OL}, $I_{OS(H)}$, and $I_{OS(L}$



Figure 2. Driver Test Circuit for I_{IH} and I_{IL}

PARAMETER MEASUREMENT INFORMATION



TEST CIRCUIT VOLTAGE WAVEFORMS

NOTES: A. C_L includes probe and jig capacitance.
B. The pulse generator has the following characteristics: t_W = 25 μs, PRR = 20 kHz, Z_O = 50 Ω, $t_r = t_f$ < 50 ns.

Figure 3. Driver Test Circuit and Voltage Waveforms



Figure 4. Receiver Test Circuit for I_{OS}



Figure 5. Receiver Test Circuit for V_{IT}, V_{OH}, and V_{OL}



TEST CIRCUIT VOLTAGE WAVEFORMS

NOTES: A. C_L includes probe and jig capacitance.
B. The pulse generator has the following characteristics: t_W = 25 μs, PRR = 20 kHz, Z_O = 50 Ω, $t_r = t_f$ < 50 ns.

Figure 6. Receiver Propagation and Transition Times

TYPICAL CHARACTERISTICS

DRIVER SECTION

VOLTAGE-TRANSFER CHARACTERISTICS



Figure 7

OUTPUT CURRENT
vs
OUTPUT VOLTAGE



Figure 8

SHORT-CIRCUIT OUTPUT CURRENT
vs
FREE-AIR TEMPERATURE



Figure 9

SLEW RATE
vs
LOAD CAPACITANCE



Figure 10

TYPICAL CHARACTERISTICS

RECEIVER SECTION

INPUT THRESHOLD VOLTAGE vs FREE-AIR TEMPERATURE



Figure 11

INPUT THRESHOLD VOLTAGE vs SUPPLY VOLTAGE



Figure 12

NOISE REJECTION



NOTE A: This figure shows the maximum amplitude of a positive-going pulse that, starting from 0 V, does not cause a change of the output level.

Figure 13

MAXIMUM SUPPLY VOLTAGE vs FREE-AIR TEMPERATURE



Figure 14

APPLICATION INFORMATION

Diodes placed in series with the V_{DD} and V_{SS} leads protect the GD75323 in the fault condition in which the device outputs are shorted to V_{DD} or V_{SS}, and the power supplies are at low and provide low-impedance paths to ground (see Figure 15).



Figure 15. Power-Supply Protection to Meet Power-Off Fault Conditions of TIA/EIA-232-F



† See Figure 10 to select the correct values for the loading capacitors (C1, C2, C3, C4, and C5), which may be required to meet the RS-232 maximum slew-rate requirement of 30 V/µs. The value of the loading capacitors required depends upon the line length and desired slew rate, but is typically 330 pF.

NOTE C: To use the receivers only, V_{DD} and V_{SS} both must be powered or tied to ground.

Figure 16. Typical Connection

PACKAGING INFORMATION

Orderable part number	Status (1)	Material type (2)	Package | Pins	Package qty | Carrier	RoHS (3)	Lead finish/ Ball material (4)	MSL rating/ Peak reflow (5)	Op temp (°C)	Part marking (6)
GD75323DW	Active	Production	SOIC (DW) | 20	25 | TUBE	Yes	NIPDAU	Level-1-260C-UNLIM	0 to 70	GD75323
GD75323DW.A	Active	Production	SOIC (DW) | 20	25 | TUBE	Yes	NIPDAU	Level-1-260C-UNLIM	0 to 70	GD75323
GD75323DWR	Active	Production	SOIC (DW) | 20	2000 | LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	0 to 70	GD75323
GD75323DWR.A	Active	Production	SOIC (DW) | 20	2000 | LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	0 to 70	GD75323

(1) **Status:** For more details on status, see our product life cycle.

(2) **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

(3) **RoHS values:** Yes, No, RoHS Exempt. See the TI RoHS Statement for additional information and value definition.

(4) **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

(5) **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

(6) **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

TUBE



*All dimensions are nominal

Device	Package Name	Package Type	Pins	SPQ	L (mm)	W (mm)	T (µm)	B (mm)
GD75323DW	DW	SOIC	20	25	507	12.83	5080	6.6
GD75323DW	DW	SOIC	20	25	506.98	12.7	4826	6.6
GD75323DW.A	DW	SOIC	20	25	507	12.83	5080	6.6
GD75323DW.A	DW	SOIC	20	25	506.98	12.7	4826	6.6



PACKAGE OUTLINE

DW0020A

SOIC - 2.65 mm max height

SOIC



NOTES:

1. All linear dimensions are in millimeters. Dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm per side.
4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.43 mm per side.
5. Reference JEDEC registration MS-013.



LAND PATTERN EXAMPLE
SCALE:6X



SOLDER MASK DETAILS

4220724/A 05/2016

NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.
7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



SOLDER PASTE EXAMPLE
BASED ON 0.125 mm THICK STENCIL
SCALE:6X

4220724/A 05/2016

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES “AS IS” AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI’s products are provided subject to TI’s Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI’s provision of these resources does not expand or otherwise alter TI’s applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2025, Texas Instruments Incorporated