

CATALOG

➔ [Cross Reference](#)[Competitive Products](#)[Military Spec P/Ns](#)[Tyco Brand P/Ns](#)

- ➔ [Part Number Search](#)
- ➔ [Document Search](#)
- ➔ [Product Type Search](#)
- ➔ [Product Family Search](#)
- ➔ [Alphabetical Search](#)
- ➔ [RoHS/ELV Compliance & Alternates](#)
- ➔ [CAD Model Search](#)
- ➔ [Brand Search](#)
- ➔ [Tool Search](#)
- ➔ [Multiple Part Comparison](#)
- ➔ [Lead Free Solutions](#)
- ➔ [Help/Glossary](#)

[Home](#)

e-bulletin newsletter
SUBSCRIBE NOW!
click here

Circuit Breakers

➔ Thermal Circuit Breakers

**W33-T1N1Q-15**  [Active](#)[Not ELV or RoHS Compliant](#)**(Corporate P/N: 3-1393248-3)**

[Search for Compliant \(RoHS/
ELV\) Alternates](#)
[Search for Parts](#)

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information

General Information	eCommerce	Related Part Information
➤ General Info ➤ Sales Info	➤ Pricing ➤ Product Availability	➤ Tooling

Searchable Features:

Brand:	Potter & Brumfield
RoHS/ELV Compliance:	Not ELV/RoHS compliant
Lead Free Solder Processes:	Not relevant for lead free process
Series:	W33
Actuator Style:	Rocker
Number of Poles:	2
Current Rating (Amps.):	15
Rocker Color:	Black (Opaque)
Circuit Function:	Poles 1 and 2 - Series Trip Overload Sensor
Operating Voltage, Max.:	50 VDC
Illuminated:	No

Other Properties:

Panel Thickness (mm [in]):	0.81 – 6.35 [0.032 – 0.250]
Panel Cutout:	22.22 x 44.45

Trip Time at 200%:	3.0 to 33 Seconds
Interrupt Capacity:	1,000 A @ 125 VAC
Termination Type:	6.35 [.250] Straight Quick Connect Tab
Stamped Marking Type:	International I/O

[Copyright](#) and [Privacy Statement](#)
Visit [Tyco International Ltd.](#)

[[Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Contact Us](#) | [About](#) | [Home](#)]