

TOSHIBA TRANSISTOR SILICON NPN TRIPLE DIFFUSED TYPE (PCT PROCESS)

# 2SC5356


SWITCHING REGULATOR APPLICATIONS  
 HIGH VOLTAGE SWITCHING APPLICATIONS  
 DC-DC CONVERTER APPLICATIONS

- Excellent Switching Times :  $t_f = 0.5 \mu s$  (Max.) ( $I_C = 1.2 A$ )
- High Collectors Breakdown Voltage :  $V_{CEO} = 800 V$
- High DC Current Gain :  $h_{FE} = 15$  (Min.) ( $I_C = 0.15 A$ )

MAXIMUM RATINGS ( $T_a = 25^\circ C$ )







CHARACTERISTIC		SYMBOL	RATING	UNIT
Collector-Base Voltage		$V_{CB0}$	900	V
Collector-Emitter Voltage		$V_{CEO}$	800	V
Emitter-Base Voltage		$V_{EBO}$	7	V
Collector Current	DC	$I_C$	3	A
	Pulse	$I_{CP}$	5	
Base Current		$I_B$	1	A
Collector Power Dissipation	$T_a = 25^\circ C$	$P_C$	1.5	W
	$T_c = 25^\circ C$		25	
Junction Temperature		$T_j$	150	$^\circ C$
Storage Temperature Range		$T_{stg}$	-55~150	$^\circ C$


Unit in mm



ELECTRICAL CHARACTERISTICS (Ta = 25°C)

CHARACTERISTIC		SYMBOL	TEST CONDITION	MIN.	TYP.	MAX.	UNIT
Collector Cut-off Current		ICBO	V <sub>CB</sub> = 720 V, I <sub>E</sub> = 0	—	—	100	μA
Emitter Cut-off Current		IEBO	V <sub>EB</sub> = 7 V, I <sub>C</sub> = 0	—	—	10	μA
Collector-Base Breakdown Voltage		V <sub>(BR)CBO</sub>	I <sub>C</sub> = 1 mA, I <sub>B</sub> = 0	900	—	—	V
Collector-Emitter Breakdown Voltage		V <sub>(BR)CEO</sub>	I <sub>C</sub> = 10 mA, I <sub>B</sub> = 0	800	—	—	V
DC Current Gain		h <sub>FE</sub> (1)	V <sub>CE</sub> = 5 V, I <sub>C</sub> = 1 mA	10	—	—	
		h <sub>FE</sub> (2)	V <sub>CE</sub> = 5 V, I <sub>C</sub> = 0.15 A	15			
Collector-Emitter Saturation Voltage		V <sub>CE(sat)</sub>	I <sub>C</sub> = 1.2 A, I <sub>B</sub> = 0.24 A	—	—	1.0	V
Base-Emitter Saturation Voltage		V <sub>BE(sat)</sub>	I <sub>C</sub> = 1.2 A, I <sub>B</sub> = 0.24 A	—	—	1.3	V
Switching Time	Rise Time	t <sub>r</sub>	<p>20 μs V<sub>CC</sub> = 360 V  <sub>IB1</sub> <sub>IB2</sub> I<sub>C</sub> 300Ω              INPUT OUTPUT</p> <p>I<sub>C</sub> = 1.2 A, I<sub>B1</sub> = 0.24 A, I<sub>B2</sub> = -0.48 A              DUTY CYCLE ≤ 1%</p>	—	—	0.7	μs
	Storage Time	t <sub>stg</sub>		—	—	4.0	
	Fall Time	t <sub>f</sub>		—	—	0.5	





**RESTRICTIONS ON PRODUCT USE**

000707EAA

- TOSHIBA is continually working to improve the quality and reliability of its products. Nevertheless, semiconductor devices in general can malfunction or fail due to their inherent electrical sensitivity and vulnerability to physical stress. It is the responsibility of the buyer, when utilizing TOSHIBA products, to comply with the standards of safety in making a safe design for the entire system, and to avoid situations in which a malfunction or failure of such TOSHIBA products could cause loss of human life, bodily injury or damage to property. In developing your designs, please ensure that TOSHIBA products are used within specified operating ranges as set forth in the most recent TOSHIBA products specifications. Also, please keep in mind the precautions and conditions set forth in the "Handling Guide for Semiconductor Devices," or "TOSHIBA Semiconductor Reliability Handbook" etc..
- The TOSHIBA products listed in this document are intended for usage in general electronics applications (computer, personal equipment, office equipment, measuring equipment, industrial robotics, domestic appliances, etc.). These TOSHIBA products are neither intended nor warranted for usage in equipment that requires extraordinarily high quality and/or reliability or a malfunction or failure of which may cause loss of human life or bodily injury ("Unintended Usage"). Unintended Usage include atomic energy control instruments, airplane or spaceship instruments, transportation instruments, traffic signal instruments, combustion control instruments, medical instruments, all types of safety devices, etc.. Unintended Usage of TOSHIBA products listed in this document shall be made at the customer's own risk.
- The information contained herein is presented only as a guide for the applications of our products. No responsibility is assumed by TOSHIBA CORPORATION for any infringements of intellectual property or other rights of the third parties which may result from its use. No license is granted by implication or otherwise under any intellectual property or other rights of TOSHIBA CORPORATION or others.
- The information contained herein is subject to change without notice.