

# F-195X

### Electrical Specifications (@25C)

1. Maximum Power: 19.63 VA
2. Primary: 115V 50/60 Hz
3. Secondary 1: 32.0VCT @ 0.250 Amps\*  
Secondary 2: 15.5VCT @ 0.750 Amps\*
4. Voltage Regulation: 5 % TYP @ full load to no load
5. Temperature Rise: 35C TYP (45C MAX allowed)

### Description:

The F-195X is part of a series which has a long history of reliable service in the field, made from a proven design and constructed with UL recognized materials.

### Construction:

Wound on a single channel nylon bobbin. Materials are UL recognized, Class B (130° C) rated.

### Safety:





These products are 100% hipot tested with an insulation of 1500V between primary and secondary windings as well as between the primary / secondary windings and the core.

### Dimensions: Units: In inches

A	B	C	D
2.250	3.750	1.875	3.125

Weight: 1.30 lbs

### Schematic:



**RoHS Compliance:** As of manufacturing date February 2005, all standard products meet the requirements of 2011/65/EU, known as the RoHS initiative.

\* Upon printing, this document is considered "uncontrolled". Please contact Triad Magnetics' website for the most current version.