


# Cylindrical High Power Surface Mount Metal Glaze™

## CHP Series

- Up to 2 watts
- Up to 1000 volts
- 0.2 ohm to 2.2 megohm range
- RoHS-compliant version available
- 150°C maximum operating temperature



 All Pb-free parts comply with EU Directive 2011/65/EU (RoHS2)

## Electrical Data

| IRC Type | Industry Foot-print | Size Code <sup>1</sup> | Maximum Power Rating      | Working Voltage <sup>2</sup> | Maximum Voltage | Resistance Range (ohms) <sup>3</sup> | Product Category | Tolerance (±%) <sup>3</sup> | TCR (ppm/°C) <sup>3</sup> |
|----------|---------------------|------------------------|---------------------------|------------------------------|-----------------|--------------------------------------|------------------|-----------------------------|---------------------------|
| CHP 1/8  | 1206                | B & C                  | 1/4W @ 70°C               | 200                          | 400             | 0.1 to 0.99                          | Low Range        | 1, 2, 5                     | 100                       |
|          |                     |                        |                           |                              |                 | 1.0 to 1.0 M                         | Standard         | 1, 2, 5                     | 50, 100                   |
|          |                     |                        |                           |                              |                 | 20 to 348K                           | Tight Tolerance  | 0.25, 0.5                   | 50, 100                   |
| CHP 1/2  | 2010                | D & E                  | 1/2W @ 70°C               | 300                          | 600             | 0.1 to 0.99                          | Low Range        | 1, 2, 5                     | 100                       |
|          |                     |                        |                           |                              |                 | 1.0 to 348K                          | Standard         | 1, 2, 5                     | 50, 100                   |
| CHP 1    | 2512                | F                      | 1W @ 70°C                 | 350                          | 700             | 0.1 to 0.99                          | Low Range        | 1, 2, 5                     | 100                       |
|          |                     |                        |                           |                              |                 | 1.0 to 2.21M                         | Standard         | 1, 2, 5                     | 50, 100                   |
|          |                     |                        |                           |                              |                 | 20 to 348K                           | Tight Tolerance  | 0.25, 0.5                   | 50, 100                   |
| CHP 2    | 3610                | H                      | 2W @ 25°C<br>1.33W @ 70°C | 500                          | 1000            | 0.2 to 0.99                          | Low Range        | 1, 2, 5                     | 100                       |
|          |                     |                        |                           |                              |                 | 1.0 to 2.21M                         | Standard         | 1, 2, 5                     | 50, 100                   |

<sup>1</sup>See pages 2 & 3 for product dimensions, recommended solder pads, and standard packaging.

<sup>2</sup>Not to exceed  $\sqrt{P \times R}$

<sup>3</sup>Consult factory for tighter TCR, tolerance, or resistance values.

## Environmental Data

| Characteristics                   | Maximum Change                       | Test Method                                                                                                        |
|-----------------------------------|--------------------------------------|--------------------------------------------------------------------------------------------------------------------|
| Thermal Shock                     | ±0.25% +.01 Ω                        | MIL-PRF-55342H, §4.8.3<br>(MIL-STD-202, Method 107G: +150°C / -65°C)                                               |
| Low Temperature Operation         | ±0.25% +.01 Ω                        | MIL-PRF-55342H, §4.8.5<br>(-65°C)                                                                                  |
| Short Time Overload               | ±0.5% +.01 Ω<br>±1% for R>100KΩ      | MIL-PRF-55342H, §4.8.6                                                                                             |
| High Temperature Exposure         | ±0.5% +.01 Ω                         | MIL-PRF-55342H, §4.8.7<br>(150°C x 100 Hours)                                                                      |
| Resistance to Bonding Exposure    | ±0.25% +.01 Ω                        | MIL-PRF-55342H, §4.8.8.2                                                                                           |
| Moisture Resistance               | ±0.5% +.01 Ω                         | MIL-PRF-55342H, §4.8.8.2<br>(MIL-STD-202, Method 106G)                                                             |
| Temperature Coefficient           | As specified                         | MIL-PRF-55342H, §4.8.10<br>(MIL-STD-202, Method 304)                                                               |
| Life Test                         | ±1% +.01 Ω                           | MIL-PRF-55342H, §4.8.11<br>(MIL-STD-202, Method 108A: 2000 Hours @ 70°C)                                           |
| Solderability                     | 95% minimum coverage                 | MIL-PRF-55342H, §4.8.12<br>(MIL-STD-202, Method 208H)                                                              |
| Terminal Adhesion Strength (push) | ±1% +.01 Ω<br>(no mechanical damage) | IRC – defined<br>1200 gram push from underside of mounted device for 60 sec                                        |
| Terminal Adhesion Strength (flex) | ±1% +.01 Ω<br>(no mechanical damage) | IRC-defined<br>Device mounted in center of 90mm long board, deflected 1 mm to exert pull on contacts for 5 seconds |

### General Note


TT Electronics reserves the right to make changes in product specification without notice or liability.

All information is subject to TT Electronics' own data and is considered accurate at time of going to print.


BI Technologies IRC Welwyn

<http://www.ttelectronics.com/resistors>

## Physical Data

| IRC Type | Size Code | Industry Footprint | Actual Size                                                                       |  |                                                             |                                 |
|----------|-----------|--------------------|-----------------------------------------------------------------------------------|------------------------------------------------------------------------------------|-------------------------------------------------------------|---------------------------------|
|          |           |                    |                                                                                   | Dimensions (Inches and (mm))                                                       |                                                             |                                 |
|          |           |                    |                                                                                   | L                                                                                  | W                                                           | C                               |
| CHP 1/8  | B         | 1206               |  | 0.128 ± 0.007<br>(3.25 ± 0.18)                                                     | 0.057 ± 0.006<br>(1.45 ± 0.15)                              | 0.020 ± 0.010<br>(0.51 ± 0.25)  |
| CHP 1/2  | D         | 2010               |  | 0.200 ± 0.010<br>(5.08 ± 0.25)                                                     | 0.079 (nom.) -0.006 / +0.011<br>(2.01 (nom.) -0.15 / +0.28) | 0.030 ± 0.010<br>(0.761 ± 0.25) |
| CHP 1    | F         | 2512               |  | 0.251 ± 0.010<br>(6.38 ± 0.25)                                                     | 0.079 (nom.) -0.006 / +0.011<br>(2.01 (nom.) -0.15 / +0.28) | 0.040 ± 0.010<br>(1.02 ± 0.25)  |
| CHP 2    | H         | 3610               |  | 0.367 ± 0.010<br>(9.32 ± 0.25)                                                     | 0.105 (nom.) -0.006 / +0.011<br>(2.67 (nom.) -0.15 / +0.28) | 0.050 ± 0.010<br>(1.27 ± 0.25)  |

## Recommended Solder Pad Dimensions (Reflow):

|  |                    |                              |                 |                 |                 |                 |                  |
|--------------------------------------------------------------------------------------|--------------------|------------------------------|-----------------|-----------------|-----------------|-----------------|------------------|
| Size Code                                                                            | Industry Footprint | Dimensions (Inches and (mm)) |                 |                 |                 |                 |                  |
|                                                                                      |                    | A                            | B               | C               | D               | E               | F                |
| B & C                                                                                | 1206               | 0.076<br>(1.93)              | 0.093<br>(2.36) | 0.058<br>(1.47) | 0.098<br>(2.49) | 0.032<br>(0.81) | 0.211<br>(5.36)  |
| D                                                                                    | 2010               | 0.111<br>(2.82)              | 0.126<br>(3.20) | 0.096<br>(2.44) | 0.152<br>(3.86) | 0.040<br>(1.02) | 0.318<br>(8.08)  |
| E                                                                                    | 2010               | 0.170<br>(4.32)              | 0.160<br>(4.06) | 0.072<br>(1.83) | 0.132<br>(3.35) | 0.044<br>(1.12) | 0.412<br>(10.46) |
| F                                                                                    | 2512               | 0.121<br>(3.07)              | 0.126<br>(3.20) | 0.127<br>(3.23) | 0.183<br>(4.65) | 0.040<br>(1.02) | 0.369<br>(9.37)  |
| H                                                                                    | 3610               | 0.170<br>(4.32)              | 0.160<br>(4.06) | 0.213<br>(5.41) | 0.273<br>(6.93) | 0.044<br>(1.12) | 0.553<br>(14.05) |

### General Note

TT Electronics reserves the right to make changes in product specification without notice or liability.  
All information is subject to TT Electronics' own data and is considered accurate at time of going to print.


CHP Series

Standard Reel Packaging per EIA-481:


| IRC Type           | Size Code | Industry Footprint | Reel Diameter* | Quantity Per Reel | Carrier Tape Width | Component Pitch |
|--------------------|-----------|--------------------|----------------|-------------------|--------------------|-----------------|
| CHP 1/8<br>MRC 1/2 | B<br>C    | 1206               | 7"             | 2,500 max.        | 8mm                | 4mm             |
|                    |           |                    | 13"            | 10,000 max.       |                    |                 |
| CHP 1/2<br>MRC 1   | D<br>E    | 2010               | 7"             | 1,500 max.        | 12mm               | 4mm             |
|                    |           |                    | 13"            | 5,000 max.        |                    |                 |
| CHP 1              | F         | 2512               | 7"             | 1,500 max.        | 12mm               | 4mm             |
|                    |           |                    | 13"            | 5,000 max.        |                    |                 |
| CHP 2              | H         | 3610               | 13"            | 1,500 max.        | 24mm               | 4mm             |

\*The 13" reel is considered standard and will be supplied unless otherwise specified.

Power Derating Curve



Repetitive Surge Curve



Note: Use for repetitive pulses where the average power dissipation is not to exceed the component rating at 70°C. Surge handling capacity for low-repetitive surges may be significantly greater than shown above. Contact factory for recommendations.

General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

## Ordering Procedure

This product has two valid part numbers:

**European (Welwyn) Part Number: CHP1-220KFI** (CHP1 with TCR  $\pm 100\text{ppm}/^\circ\text{C}$  at 220 kilohms  $\pm 1\%$ , Pb-free)

|   |   |   |   |  |  |   |   |   |   |   |   |   |
|---|---|---|---|--|--|---|---|---|---|---|---|---|
| C | H | P | 1 |  |  | - | 2 | 2 | 0 | K | F | I |
| 1 |   |   | 2 |  |  | 3 |   |   | 4 | 5 |   |   |

| 1<br>Type | 2<br>TCR (ppm/°C) | 3<br>Value                             | 4<br>Tolerance | 5<br>Termination & Packing |      |               |
|-----------|-------------------|----------------------------------------|----------------|----------------------------|------|---------------|
| CHP1/8    | Omit for ±100     | E24 = 3/4 characters                   | C = ±0.25%     | I = Pb-free, Tape Pack     |      |               |
| CHP1/2    | -50 = ±50         | E96 = 4/5 characters                   | D = ±0.5%      | PB = SnPb, Tape Pack       |      |               |
| CHP1      |                   | R = ohms<br>K = kilohms<br>M = megohms | F = ±1%        | CHP1/8                     | Tape | 2500/7" reel  |
| CHP2      |                   |                                        | G = ±2%        | CHP1/2, 1                  |      | 1500/7" reel  |
|           |                   |                                        | J = ±5%        | CHP2                       |      | 1500/13" reel |

**USA (IRC) Part Number: CHP11002203FLF** (CHP1 with TCR  $\pm 100\text{ppm}/^\circ\text{C}$  at 220 kilohms  $\pm 1\%$ , Pb-free)

|   |   |   |   |   |   |   |   |   |   |   |   |   |   |
|---|---|---|---|---|---|---|---|---|---|---|---|---|---|
| C | H | P | 1 | 1 | 0 | 0 | 2 | 2 | 0 | 3 | F | L | F |
| 1 |   |   | 2 |   |   | 3 |   |   | 4 | 5 |   |   |   |

| 1<br>Type | 2<br>TCR   | 3<br>Value                                                | 4<br>Tolerance | 5<br>Termination & Packing   |               |
|-----------|------------|-----------------------------------------------------------|----------------|------------------------------|---------------|
| CHP1/8    | 50 = ±50   | 3 digits + multiplier<br>R = ohms for<br>values <100 ohms | C = ±0.25%     | Omit for SnPb, Standard pack |               |
| CHP1/2    | 100 = ±100 |                                                           | D = ±0.5%      | LF = Pb-free, Standard pack  |               |
| CHP1      |            |                                                           | F = ±1%        | CHP1/8                       | 2500/7" reel  |
| CHP2      |            |                                                           | G = ±2%        | CHP1/2 & 1                   | 1500/7" reel  |
|           |            |                                                           | J = ±5%        | CHP2                         | 1500/13" reel |

### General Note

TT Electronics reserves the right to make changes in product specification without notice or liability.  
All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## TT Electronics:

[CHP1/8-50-2R00-F](#) [CHP1-100-3013-F](#) [CHP1-100-90R9-F](#) [CHP1-100-1R82-F](#) [CHP1-100-3900-J](#) [CHP1-100-1003-F](#)  
[CHP1/2-100-4992-F](#) [CHP1-100-4020-F](#) [CHP1-100-1002-J](#) [CHP1-100-1002-F](#) [CHP1-100-6202-G](#) [CHP1-100-3R00-J](#)  
[CHP1-100-R270-F](#) [CHP1-100-1R30-F](#) [CHP1-100-3R00-F](#) [CHP1-100-1502-J](#) [CHP1/8-100-1003-J](#) [CHP1/8-100-](#)  
[1001-F](#) [CHP1-100-5R60-F](#) [CHP1-50-50R0-D](#) [CHP1/8-100-1001-J](#) [CHP1-100-1000-F](#) [CHP1-100-2740-F](#) [CHP1/8-](#)  
[100-1R30-F](#) [CHP1-100-5600-J](#) [CHP1/8-100-1000-G](#) [CHP1-100-R200-F](#) [CHP1/8-100-1000-J](#) [CHP1/8-100-1000-F](#)  
[CHP1/2-100-2R40-J](#) [CHP1/2-100-1001-J](#) [CHP1/8-50-1001-F-7](#) [CHP1-100-5360-F](#) [CHP1/8-100-47R0-J](#) [CHP1/8-100-](#)  
[2002-J](#) [CHP1-100-12R0-J](#) [CHP1/8-100-4421-F](#) [CHP1-100-4R02-F](#) [CHP1/8-100-5102-G](#) [CHP1-100-2000-F](#) [CHP1-](#)  
[100-2000-J](#) [CHP1-100-39R0-F](#) [CHP1-100-3300-F](#) [CHP1-100-3300-J](#) [CHP1/8-100-3R32-F](#) [CHP1-100-6191-F](#) [CHP1-](#)  
[100-75R0-J](#) [CHP1/8-50-10R0-F](#) [CHP2-100-5001-F](#) [CHP1-100-36R0-J](#) [CHP1-100-3601-J](#) [CHP1-100-3001-J](#) [CHP1-](#)  
[100-1621-F](#) [CHP1/2-100-2002-J](#) [CHP1-100-47R5-F](#) [CHP1-100-10R0-J](#) [CHP1-100-10R0-F](#) [CHP1-50-1000-F](#)  
[CHP1/2-100-15R0-J](#) [CHP1-100-1330-F](#) [CHP1-50-1002-F](#) [CHP1-100-33R2-F](#) [CHP1-100-3600-J](#) [CHP1/8-100-R330-F](#)  
[CHP1/8-100-1501-F](#) [CHP1/8-100-6043-F](#) [CHP1-100-1201-J](#) [CHP1-100-1001-J](#) [CHP1/2-100-5000-J](#) [CHP1/8-100-](#)  
[R500-J](#) [CHP1/8-100-2003-F](#) [CHP1-50-40R2-F](#) [CHP1/2-100-6810-F](#) [CHP1-100-1603-J](#) [CHP1-100-3320-F](#) [CHP1-](#)  
[100-R180-F](#) [CHP1/2-100-10R0-J](#) [CHP2-100-3001-J-13](#) [CHP1-50-75R0-F](#) [CHP1/8-100-10R0-J](#) [CHP1/8-100-10R0-F](#)  
[CHP1/8-100-22R0-J](#) [CHP1-100-1R50-J](#) [CHP1-100-1R50-F](#) [CHP1/8-100-R400-F](#) [CHP1/8-100-1900-J](#) [CHP1-100-](#)  
[2R00-F](#) [CHP1-100-5603-J](#) [CHP1-100-4R70-J](#) [CHP1/2-100-1R00-F](#) [CHP1/8-100-1500-J](#) [CHP1/8-100-1500-G](#) [CHP1-](#)  
[100-R330-F](#) [CHP1/2-100-1000-G](#) [CHP1/2-100-1000-F](#) [CHP1/2-100-1000-J](#) [CHP2-100-5600-F](#) [CHP1/8-100-20R0-J](#)  
[CHP1-100-3R32-F](#) [CHP1/2-100-3503-F](#)