

## TPS3809x 3-Pin Supply Voltage Supervisors

### 1 Features

- 3-pin SOT-23 package
- Supply current of 9  $\mu\text{A}$  (typical)
- Precision supply voltage monitor  
2.5 V, 3 V, 3.3 V, 5 V
- Pin-for-pin compatible with MAX 809
- Temperature range:  $-40^{\circ}\text{C}$  to  $+85^{\circ}\text{C}$

### 2 Applications

- [Factory automation](#)
- [Wireless speakers](#)
- [Motor drives](#)
- [Servers](#)
- [Appliances](#)
- [Electricity meters](#)
- [Building automation](#)

### 3 Description

The TPS3809 family of supervisory circuits provides circuit initialization and timing supervision, primarily for DSPs and processor-based systems. The newer [TLV809E](#) device is an alternative with the same pins, functions and electrical parameters.


During power-on,  $\overline{\text{RESET}}$  is asserted when the supply voltage  $V_{\text{DD}}$  becomes higher than 1.1 V. Thereafter, the supervisory circuit monitors  $V_{\text{DD}}$  and keeps  $\overline{\text{RESET}}$  active as long as  $V_{\text{DD}}$  remains below the threshold voltage  $V_{\text{IT}}$ . An internal timer delays the return of the output to the inactive state (high) to ensure proper system reset. The delay time,  $t_{\text{d(typ)}} = 200 \text{ ms}$ , starts after  $V_{\text{DD}}$  has risen above the threshold voltage  $V_{\text{IT}}$ . When the supply voltage drops below the threshold voltage  $V_{\text{IT}}$ , the output becomes active (low) again. No external components are required. All the devices of this family have a fixed sense-threshold voltage  $V_{\text{IT}}$  set by an internal voltage divider.

The product spectrum is designed for supply voltages of 2.5 V, 3 V, 3.3 V, and 5 V. The circuits are available in a 3-pin SOT-23. The TPS3809 devices are characterized for operation over a temperature range of  $-40^{\circ}\text{C}$  to  $85^{\circ}\text{C}$ .

#### Device Information

| PART NUMBER | PACKAGE <sup>(1)</sup> | BODY SIZE (NOM)          |
|-------------|------------------------|--------------------------|
| TPS3809     | SOT-23 (3), DBV        | 2.90 mm $\times$ 1.60 mm |

(1) For all available packages, see the orderable addendum at the end of the data sheet.



**Typical Application**



## Table of Contents

|                                                                  |          |                                                |          |
|------------------------------------------------------------------|----------|------------------------------------------------|----------|
| <b>1 Features</b> .....                                          | <b>1</b> | 7.3 Dissipation Ratings.....                   | <b>5</b> |
| <b>2 Applications</b> .....                                      | <b>1</b> | 7.4 Electrical Characteristics.....            | <b>5</b> |
| <b>3 Description</b> .....                                       | <b>1</b> | 7.5 Timing Requirements.....                   | <b>6</b> |
| <b>4 Revision History</b> .....                                  | <b>2</b> | 7.6 Switching Characteristics.....             | <b>6</b> |
| <b>5 Device Comparison</b> .....                                 | <b>3</b> | 7.7 Timing Diagram.....                        | <b>6</b> |
| <b>6 Pin Configuration and Functions</b> .....                   | <b>4</b> | 7.8 Typical Characteristics.....               | <b>7</b> |
| <b>7 Specifications</b> .....                                    | <b>5</b> | <b>8 Detailed Description</b> .....            | <b>9</b> |
| 7.1 Absolute Maximum Ratings <sup>(1)</sup> <sup>(2)</sup> ..... | <b>5</b> | <b>9 Electrostatic Discharge Caution</b> ..... | <b>9</b> |
| 7.2 Recommended Operating Conditions.....                        | <b>5</b> |                                                |          |

## 4 Revision History

|                                                                                                                                                                                      |             |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------|
| <b>Changes from Revision C (October 2013) to Revision D (January 2021)</b>                                                                                                           | <b>Page</b> |
| • Updated the numbering format for tables, figures, and cross-references throughout the document.....                                                                                | <b>1</b>    |
| • Added new sentence regarding the new TLV809E to the <i>Description</i> section.....                                                                                                | <b>1</b>    |
| • Added the pinout and pin function table.....                                                                                                                                       | <b>4</b>    |
| • Changed VDD from 7 to 6.5 in <i>Absolute Maximum Ratings</i> .....                                                                                                                 | <b>5</b>    |
| • Changed V <sub>OL</sub> @ 500μA from 0.2 to 0.3V and corrected header of the table from TPS3800-xx, TPS3801-xx, TPS3802-xx to TPS3809xx in <i>Electrical Characteristics</i> ..... | <b>5</b>    |
| • Changed t <sub>w</sub> pulse duration from 3 to 10μs in <i>Timing Requirements</i> .....                                                                                           | <b>6</b>    |
| • Changed t <sub>PHL</sub> from 1 to 10μs in <i>Switching Characteristics</i> .....                                                                                                  | <b>6</b>    |
| <b>Changes from Revision B (July 2012) to Revision C (October 2013)</b>                                                                                                              | <b>Page</b> |
| • Changed front page and page flow to match current standard look and feel.....                                                                                                      | <b>1</b>    |
| • Changed "Operating junction temperature range" to "Operating free-air temperature range" in Absolute Maximum Ratings (typo).....                                                   | <b>5</b>    |
| <b>Changes from Revision A (October 2010) to Revision B (July 2012)</b>                                                                                                              | <b>Page</b> |
| • Changed the Pull-up resistor value, $\overline{\text{RESET}}$ To: $\overline{\text{RESET}}$ current sink during startup in the Recommended Operating Conditions Table.....         | <b>5</b>    |
| <b>Changes from Revision * (August 1999) to Revision A (October 2010)</b>                                                                                                            | <b>Page</b> |
| • Added Pull-up resistor value, $\overline{\text{RESET}}$ to the Recommended Operating Conditions Table.....                                                                         | <b>5</b>    |

## 5 Device Comparison


**Table 5-1. Device Comparison Table**

| T <sub>A</sub> | DEVICE NAME    |                | THRESHOLD VOLTAGE | MARKING |
|----------------|----------------|----------------|-------------------|---------|
| –40°C to 85°C  | TPS3809J25DBVR | TPS3809J25DBVT | 2.25 V            | PCZI    |
|                | TPS3809L30DBVR | TPS3809L30DBVT | 2.64 V            | PDAI    |
|                | TPS3809K33DBVR | TPS3809K33DBVT | 2.93 V            | PDBI    |
|                | TPS3809I50DBVR | TPS3809I50DBVT | 4.55 V            | PDCI    |


**FUNCTION/TRUTH TABLE, TPS3809**

| V <sub>DD</sub> >V <sub>IT</sub> | $\overline{\text{RESET}}$ |
|----------------------------------|---------------------------|
| 0                                | L                         |
| 1                                | H                         |

**ORDERING INFORMATION**



## 6 Pin Configuration and Functions



**Figure 6-1. Pin configuration**

**Table 6-1. Pin Functions**

| PIN   |     | I/O <sup>(1)</sup> | DESCRIPTION                                                                                                                                                                                                                                           |
|-------|-----|--------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| NAME  | NO. |                    |                                                                                                                                                                                                                                                       |
| GND   | 1   | -                  | This pin should be connected to ground with a low-impedance connection.                                                                                                                                                                               |
| RESET | 2   | O                  | RESET is an active low signal, asserting when V <sub>DD</sub> is below the threshold voltage. When V <sub>DD</sub> rises above V <sub>IT</sub> , there is a delay time (t <sub>d</sub> ) until RESET deasserts.<br>RESET is a push-pull output stage. |
| VDD   | 3   | -                  | Supply voltage pin. A 0.1-μF ceramic capacitor from this pin to ground is recommended to improve stability of the threshold voltage                                                                                                                   |

## 7 Specifications

### 7.1 Absolute Maximum Ratings <sup>(1)</sup> <sup>(2)</sup>

Over operating free-air temperature range (unless otherwise noted).

|                                                                | UNIT                         |
|----------------------------------------------------------------|------------------------------|
| Supply voltage, $V_{DD}$                                       | 6.5 V                        |
| All other pins                                                 | –0.3 V to 6.5 V              |
| Maximum low-output current, $I_{OL}$                           | 5 mA                         |
| Maximum high-output current, $I_{OH}$                          | –5 mA                        |
| Input-clamp current, $I_{IK}$ ( $V_I < 0$ or $V_I > V_{DD}$ )  | ±20 mA                       |
| Output-clamp current, $I_{OK}$ ( $V_O < 0$ or $V_O > V_{DD}$ ) | ±20 mA                       |
| Continuous total power dissipation                             | See Dissipation Rating Table |
| Operating free-air temperature range, $T_A$                    | –40°C to 85°C                |
| Storage temperature range, $T_{stg}$                           | –65°C to 150°C               |

- (1) Stresses beyond those listed under *absolute maximum ratings* may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under *recommended operating conditions* is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.
- (2) All voltage values are with respect to GND. For reliable operation, the device should not be operated at 6.5 V for more than  $t = 1000h$  continuously.

### 7.2 Recommended Operating Conditions

|                                             | MIN | MAX | UNIT |
|---------------------------------------------|-----|-----|------|
| Supply voltage, $V_{DD}$                    | 2   | 6   | V    |
| RESET current sink during startup           |     | 50  | μA   |
| Operating free-air temperature range, $T_A$ | –40 | +85 | °C   |

### 7.3 Dissipation Ratings

| PACKAGE | $T_A < 25^\circ\text{C}$<br>POWER RATING | DERATING FACTOR<br>ABOVE $T_A < 25^\circ\text{C}$ | $T_A = 70^\circ\text{C}$<br>POWER RATING | $T_A = 85^\circ\text{C}$<br>POWER RATING |
|---------|------------------------------------------|---------------------------------------------------|------------------------------------------|------------------------------------------|
| DBV     | 437 mW                                   | 3.5 mW/°C                                         | 280 mW                                   | 227 mW                                   |

### 7.4 Electrical Characteristics

Over recommended operating free-air temperature range (unless otherwise noted).

| PARAMETER                                                              |            | TEST CONDITIONS                                          | TPS3809xx            |      |      | UNIT |
|------------------------------------------------------------------------|------------|----------------------------------------------------------|----------------------|------|------|------|
|                                                                        |            |                                                          | MIN                  | TYP  | MAX  |      |
| V <sub>OH</sub> High-level output voltage                              |            | V <sub>DD</sub> = 2.5 V to 6 V I <sub>OH</sub> = −500 μA | V <sub>DD</sub> −0.2 |      |      | V    |
|                                                                        |            | V <sub>DD</sub> = 3.3 V I <sub>OH</sub> = −2 mA          | V <sub>DD</sub> −0.4 |      |      |      |
|                                                                        |            | V <sub>DD</sub> = 6 V I <sub>OH</sub> = −4 mA            | V <sub>DD</sub> −0.4 |      |      |      |
| V <sub>OL</sub> Low-level output voltage                               |            | V <sub>DD</sub> = 2 V to 6 V, I <sub>OL</sub> = 500 μA   | 0.3                  |      |      | V    |
|                                                                        |            | V <sub>DD</sub> = 3.3 V, I <sub>OL</sub> = 2 mA          | 0.4                  |      |      |      |
|                                                                        |            | V <sub>DD</sub> = 6 V, I <sub>OL</sub> = 4 mA            | 0.4                  |      |      |      |
| Power-up reset voltage <sup>(1)</sup>                                  |            | V <sub>DD</sub> ≥ 1.1 V, I <sub>OL</sub> = 50 μA         | 0.2                  |      |      | V    |
| V <sub>IT−</sub> Negative-going input threshold voltage <sup>(2)</sup> | TPS3809J25 | T <sub>A</sub> = −40°C to 85°C                           | 2.2                  | 2.25 | 2.3  | V    |
|                                                                        | TPS3809L30 |                                                          | 2.58                 | 2.64 | 2.7  |      |
|                                                                        | TPS3809K33 |                                                          | 2.87                 | 2.93 | 2.99 |      |
|                                                                        | TPS3809I50 |                                                          | 4.45                 | 4.55 | 4.65 |      |
| V <sub>hys</sub> Threshold hysteresis                                  | TPS3809J25 |                                                          | 30                   |      |      | mV   |
|                                                                        | TPS3809L30 |                                                          | 35                   |      |      |      |
|                                                                        | TPS3809K33 |                                                          | 40                   |      |      |      |
|                                                                        | TPS3809I50 |                                                          | 60                   |      |      |      |

Over recommended operating free-air temperature range (unless otherwise noted).

| PARAMETER               |  | TEST CONDITIONS                            | TPS3809xx |     |     | UNIT          |
|-------------------------|--|--------------------------------------------|-----------|-----|-----|---------------|
|                         |  |                                            | MIN       | TYP | MAX |               |
| $I_{DD}$ Supply current |  | $V_{DD} = 2\text{ V}$ , output unconnected |           | 9   | 12  | $\mu\text{A}$ |
|                         |  | $V_{DD} = 6\text{ V}$ , output unconnected |           | 20  | 25  |               |
| $C_i$ Input capacitance |  | $V_i = 0\text{ V}$ to $V_{DD}$             |           | 5   |     | $\text{pF}$   |

- (1) The lowest supply voltage at which  $\overline{\text{RESET}}$  becomes active.  $t_r, V_{DD} \geq 15\text{ }\mu\text{s/V}$ .
- (2) To ensure the best stability of the threshold voltage, a bypass capacitor (0.1- $\mu\text{F}$  ceramic) should be placed near the supply terminals.

## 7.5 Timing Requirements

at  $R_L = 1\text{ M}\Omega$ ,  $C_L = 50\text{ pF}$ ,  $T_A = 25^\circ\text{C}$


| PARAMETER         |             | TEST CONDITIONS                                                       | MIN | TYP | MAX | UNIT          |
|-------------------|-------------|-----------------------------------------------------------------------|-----|-----|-----|---------------|
| $t_w$ Pulse width | at $V_{DD}$ | $V_{DD} = V_{IT-} + 0.2\text{ V}$ , $V_{DD} = V_{IT-} - 0.2\text{ V}$ | 10  |     |     | $\mu\text{s}$ |

## 7.6 Switching Characteristics

at  $R_L = 1\text{ M}\Omega$ ,  $C_L = 50\text{ pF}$ ,  $T_A = 25^\circ\text{C}$

| PARAMETER                                                    |                                             | TEST CONDITIONS                                                              | MIN | TYP | MAX | UNIT          |
|--------------------------------------------------------------|---------------------------------------------|------------------------------------------------------------------------------|-----|-----|-----|---------------|
| $t_d$ Delay time                                             |                                             | $V_{DD} \geq V_{IT-} + 0.2\text{ V}$ ,<br>See <a href="#">timing diagram</a> | 120 | 200 | 280 | $\text{ms}$   |
| $t_{PHL}$ Propagation (delay) time, high-to-low-level output | $V_{DD}$ to $\overline{\text{RESET}}$ delay | $V_{IL} = V_{IT-} - 0.2\text{ V}$ ,<br>$V_{IH} = V_{IT-} + 0.2\text{ V}$     |     | 10  |     | $\mu\text{s}$ |

## 7.7 Timing Diagram



## 7.8 Typical Characteristics




Figure 7-1. LOW-LEVEL OUTPUT VOLTAGE vs LOW-LEVEL OUTPUT CURRENT




Figure 7-2. SUPPLY CURRENT vs SUPPLY VOLTAGE




Figure 7-3. HIGH-LEVEL OUTPUT VOLTAGE vs HIGH-LEVEL OUTPUT CURRENT at  $V_{DD}=6V$




Figure 7-4. HIGH-LEVEL OUTPUT VOLTAGE vs HIGH-LEVEL OUTPUT CURRENT at  $V_{DD}=2.5V$

## 7.8 Typical Characteristics (continued)





Figure 7-5. NORMALIZED INPUT THRESHOLD VOLTAGE vs FREE-AIR TEMPERATURE AT  $V_{DD}=2.3\text{V}$

## 8 Detailed Description



## 9 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

## PACKAGING INFORMATION

| Orderable part number          | Status<br>(1) | Material type<br>(2) | Package   Pins   | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6) |
|--------------------------------|---------------|----------------------|------------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| <a href="#">TPS3809I50DBVR</a> | Active        | Production           | SOT-23 (DBV)   3 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | PDCI                |
| TPS3809I50DBVR.A               | Active        | Production           | SOT-23 (DBV)   3 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | PDCI                |
| TPS3809I50DBVR1G4              | Active        | Production           | SOT-23 (DBV)   3 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | PDCI                |
| TPS3809I50DBVR1G4.A            | Active        | Production           | SOT-23 (DBV)   3 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | PDCI                |
| TPS3809I50DBVRG4               | Active        | Production           | SOT-23 (DBV)   3 | 3000   LARGE T&R      | -           | Call TI                              | Call TI                           | -40 to 85    |                     |
| <a href="#">TPS3809I50DBVT</a> | Active        | Production           | SOT-23 (DBV)   3 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | PDCI                |
| TPS3809I50DBVT.A               | Active        | Production           | SOT-23 (DBV)   3 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | PDCI                |
| <a href="#">TPS3809J25DBVR</a> | Active        | Production           | SOT-23 (DBV)   3 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | PCZI                |
| TPS3809J25DBVR.A               | Active        | Production           | SOT-23 (DBV)   3 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | PCZI                |
| TPS3809J25DBVRG4               | Active        | Production           | SOT-23 (DBV)   3 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | PCZI                |
| TPS3809J25DBVRG4.A             | Active        | Production           | SOT-23 (DBV)   3 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | PCZI                |
| <a href="#">TPS3809J25DBVT</a> | Active        | Production           | SOT-23 (DBV)   3 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | PCZI                |
| TPS3809J25DBVT.A               | Active        | Production           | SOT-23 (DBV)   3 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | PCZI                |
| <a href="#">TPS3809K33DBVR</a> | Active        | Production           | SOT-23 (DBV)   3 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | PDBI                |
| TPS3809K33DBVR.A               | Active        | Production           | SOT-23 (DBV)   3 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | PDBI                |
| TPS3809K33DBVR1G4              | Active        | Production           | SOT-23 (DBV)   3 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | PDBI                |
| TPS3809K33DBVR1G4.A            | Active        | Production           | SOT-23 (DBV)   3 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | PDBI                |
| TPS3809K33DBVRG4               | Active        | Production           | SOT-23 (DBV)   3 | 3000   LARGE T&R      | -           | Call TI                              | Call TI                           | -40 to 85    |                     |
| <a href="#">TPS3809K33DBVT</a> | Active        | Production           | SOT-23 (DBV)   3 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | PDBI                |
| TPS3809K33DBVT.A               | Active        | Production           | SOT-23 (DBV)   3 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | PDBI                |
| <a href="#">TPS3809L30DBVR</a> | Active        | Production           | SOT-23 (DBV)   3 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | PDAI                |
| TPS3809L30DBVR.A               | Active        | Production           | SOT-23 (DBV)   3 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | PDAI                |
| TPS3809L30DBVR1G4              | Active        | Production           | SOT-23 (DBV)   3 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | PDAI                |
| TPS3809L30DBVR1G4.A            | Active        | Production           | SOT-23 (DBV)   3 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | PDAI                |
| TPS3809L30DBVRG4               | Active        | Production           | SOT-23 (DBV)   3 | 3000   LARGE T&R      | -           | Call TI                              | Call TI                           | -40 to 85    |                     |
| <a href="#">TPS3809L30DBVT</a> | Active        | Production           | SOT-23 (DBV)   3 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | PDAI                |
| TPS3809L30DBVT.A               | Active        | Production           | SOT-23 (DBV)   3 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | PDAI                |

<sup>(1)</sup> **Status:** For more details on status, see our [product life cycle](#).

<sup>(2)</sup> **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

<sup>(3)</sup> **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

<sup>(4)</sup> **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

<sup>(5)</sup> **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

<sup>(6)</sup> **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "-" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

#### **OTHER QUALIFIED VERSIONS OF TPS3809 :**

- Automotive : [TPS3809-Q1](#)
- Enhanced Product : [TPS3809-EP](#)

NOTE: Qualified Version Definitions:


- Automotive - Q100 devices qualified for high-reliability automotive applications targeting zero defects
- Enhanced Product - Supports Defense, Aerospace and Medical Applications

**TAPE AND REEL INFORMATION**


\*All dimensions are nominal

| Device            | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|-------------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| TPS3809I50DBVR    | SOT-23       | DBV             | 3    | 3000 | 178.0              | 9.0                | 3.3     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS3809I50DBVR1G4 | SOT-23       | DBV             | 3    | 3000 | 178.0              | 9.0                | 3.3     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS3809I50DBVT    | SOT-23       | DBV             | 3    | 250  | 178.0              | 9.0                | 3.3     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS3809J25DBVR    | SOT-23       | DBV             | 3    | 3000 | 178.0              | 9.0                | 3.3     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS3809J25DBVRG4  | SOT-23       | DBV             | 3    | 3000 | 178.0              | 9.0                | 3.3     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS3809J25DBVT    | SOT-23       | DBV             | 3    | 250  | 178.0              | 9.0                | 3.3     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS3809K33DBVR    | SOT-23       | DBV             | 3    | 3000 | 178.0              | 9.0                | 3.3     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS3809K33DBVR1G4 | SOT-23       | DBV             | 3    | 3000 | 178.0              | 9.0                | 3.3     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS3809K33DBVT    | SOT-23       | DBV             | 3    | 250  | 178.0              | 9.0                | 3.3     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS3809L30DBVR    | SOT-23       | DBV             | 3    | 3000 | 178.0              | 9.0                | 3.3     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS3809L30DBVR1G4 | SOT-23       | DBV             | 3    | 3000 | 178.0              | 9.0                | 3.3     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TPS3809L30DBVT    | SOT-23       | DBV             | 3    | 250  | 178.0              | 9.0                | 3.3     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |

## TAPE AND REEL BOX DIMENSIONS



\*All dimensions are nominal

| Device            | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|-------------------|--------------|-----------------|------|------|-------------|------------|-------------|
| TPS3809I50DBVR    | SOT-23       | DBV             | 3    | 3000 | 180.0       | 180.0      | 18.0        |
| TPS3809I50DBVR1G4 | SOT-23       | DBV             | 3    | 3000 | 180.0       | 180.0      | 18.0        |
| TPS3809I50DBVT    | SOT-23       | DBV             | 3    | 250  | 180.0       | 180.0      | 18.0        |
| TPS3809J25DBVR    | SOT-23       | DBV             | 3    | 3000 | 180.0       | 180.0      | 18.0        |
| TPS3809J25DBVRG4  | SOT-23       | DBV             | 3    | 3000 | 180.0       | 180.0      | 18.0        |
| TPS3809J25DBVT    | SOT-23       | DBV             | 3    | 250  | 180.0       | 180.0      | 18.0        |
| TPS3809K33DBVR    | SOT-23       | DBV             | 3    | 3000 | 180.0       | 180.0      | 18.0        |
| TPS3809K33DBVR1G4 | SOT-23       | DBV             | 3    | 3000 | 180.0       | 180.0      | 18.0        |
| TPS3809K33DBVT    | SOT-23       | DBV             | 3    | 250  | 180.0       | 180.0      | 18.0        |
| TPS3809L30DBVR    | SOT-23       | DBV             | 3    | 3000 | 180.0       | 180.0      | 18.0        |
| TPS3809L30DBVR1G4 | SOT-23       | DBV             | 3    | 3000 | 180.0       | 180.0      | 18.0        |
| TPS3809L30DBVT    | SOT-23       | DBV             | 3    | 250  | 180.0       | 180.0      | 18.0        |



## SOT-23 - 1.45 mm max height

## SMALL OUTLINE TRANSISTOR




1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. Reference JEDEC MO-178.
4. Body dimensions do not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.25 mm per side.
5. Support pin may differ or may not be present.

# EXAMPLE BOARD LAYOUT


DBV0003A

SOT-23 - 1.45 mm max height

SMALL OUTLINE TRANSISTOR



LAND PATTERN EXAMPLE  
EXPOSED METAL SHOWN  
SCALE:15X



SOLDER MASK DETAILS

4220743/D 08/2024

NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.


7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

## EXAMPLE STENCIL DESIGN

DBV0003A

SOT-23 - 1.45 mm max height

SMALL OUTLINE TRANSISTOR



SOLDER PASTE EXAMPLE  
BASED ON 0.125 mm THICK STENCIL  
SCALE:15X

4220743/D 08/2024

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you fully indemnify TI and its representatives against any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#), [TI's General Quality Guidelines](#), or other applicable terms available either on [ti.com](#) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products. Unless TI explicitly designates a product as custom or customer-specified, TI products are standard, catalog, general purpose devices.

TI objects to and rejects any additional or different terms you may propose.

Copyright © 2025, Texas Instruments Incorporated

Last updated 10/2025