

ELECTRICAL CHARACTERISTICS (T_{amb} = 25°C unless otherwise stated)

Parameter	Test Conditions ¹	Min.	Typ.	Max.	Unit	
INDIVIDUAL TRANSISTOR CHARACTERISTICS						
V _{(BR)CBO}	Collector – Base Breakdown Voltage	I _C = 10μA	I _E = 0	45	V	
V _{(BR)CEO*}	Collector – Emitter Breakdown Voltage	I _C = 10mA	I _B = 0	45		
V _{(BR)EBO}	Emitter – Base Breakdown Voltage	I _E = 10μA	I _C = 0	6		
I _{CBO}	Collector Cut-off Current	V _{CB} = 45V	I _E = 0		10	nA
			T _A = 150°C			10
I _{CEO}	Collector Cut-off Current	V _{CE} = 5V	I _B = 0		2	nA
I _{EBO}	Emitter Cut-off Current	V _{EB} = 5V	I _C = 0		2	nA
h _{FE}	DC Current Gain	V _{CE} = 5V	I _C = 10μA	150	600	—
				T _A = -55°C	30	
			I _C = 100μA	225		
		V _{CE} = 5V	I _C = 1mA	300		
V _{BE}	Base – Emitter Voltage	V _{CE} = 5V	I _C = 100μA		0.70	V
V _{CE(sat)}	Collector – Emitter Saturation Voltage	I _B = 100μA	I _C = 1mA		0.35	
h _{ib}	Small Signal Common – Base Input Impedance	V _{CB} = 5V	I _C = 1mA	25	32	Ω
		f = 1kHz				
h _{ob}	Small Signal Common – Base Output Admittance	V _{CB} = 5V	I _C = 1mA		1	μmho
		f = 1kHz				
h _{fe}	Small Signal Common – Base Current Gain	V _{CE} = 5V	I _C = 500μA	3		—
		f = 20MHz				
C _{obo}	Common – Base Open Circuit Output Capacitance	V _{CB} = 5V	I _E = 0		6	pF
		f = 140kHz to 1MHz				

* Pulse Test: t_p = 300μs, δ ≤ 1%.

Parameter	Test Conditions	2N2916			2N2918			Unit
		Min.	Typ.	Max.	Min.	Typ.	Max.	
TRANSISTOR MATCHING CHARACTERISTICS								
h _{FE1}	Static Forward Current	V _{CE} = 5V	I _C = 100μA	0.9	1	0.8	1	—
h _{FE2}	Gain Balance Ratio	See Note 2.						
V _{BE1} - V _{BE2}	Base – Emitter Voltage Differential	V _{CE} = 5V	I _C = 100μA		3		5	mV
		V _{CE} = 5V	I _C = 10μA to 1mA		5		10	
Δ(V _{BE1} - V _{BE2})ΔT _A	Base – Emitter Voltage Differential Change With Temperature	V _{CE} = 5V	I _C = 100μA		0.8		1.6	mV
		T _{A1} = 25°C	T _{A2} = -55°C					
		V _{CE} = 5V	I _C = 100μA		1		2	
		T _{A1} = 25°C	T _{A2} = 125°C					

NOTES

- 1) Terminals not under test are open circuited under all test conditions.
- 2) The lower of the two readings is taken as h_{FE1}.