




Features

- > High precision and high frequency stability.
- > Excellent heat resistance and environmental characteristics.
- > Applications in PDA, DSC, DVC, and PC.
- > RoHS Compliant / Pb Free.


Electrical Specifications

Item / Type	8Z
Frequency Range	14 ~ 54 MHz
Frequency Tolerance (at 25 °C)	± 10 ppm, ± 30 ppm, or specify
Frequency Stability Over Operating Temperature Range	± 10 ppm, ± 30 ppm, or specify
Operating Temperature Range	-10 ~ +70 °C, or specify
Shunt Capacitance (C0)	3 pF Max.
Drive Level	1 ~ 100 µW Max. (10 µW typical)
Load Capacitance	8 pF, 10 pF, 12 pF, or specify
Aging (at 25 °C)	± 3 ppm / year Max.
Storage Temperature Range	- 40 ~ + 85 °C

Equivalent Series Resistance(ESR)

Fundamental	
14 ~ 30 MHz	100 Ω Max.
30 ~ 54 MHz	60 Ω Max.

Dimensions



Units:mm

Remark : Specification subject to change without prior notice. Please confirm with our sales. <http://www.txccorp.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TXC Corporation:](#)

[8Z-14.31818MAAJ-T](#) [8Z-16.000MAAJ-T](#) [8Z-16.000MEEQ-T](#) [8Z-20.000MAAJ-T](#) [8Z-20.000MEEQ-T](#) [8Z-24.000MAAJ-T](#) [8Z-24.000MEEQ-T](#) [8Z-25.000MAAJ-T](#) [8Z-25.000MEEQ-T](#) [8Z-26.000MAAJ-T](#) [8Z-26.000MEEQ-T](#) [8Z-27.000MAAJ-T](#) [8Z-27.000MEEQ-T](#) [8Z-38.400MAAJ-T](#) [8Z-38.400MEEQ-T](#) [8Z-40.000MAAJ-T](#) [8Z-40.000MEEQ-T](#) [8Z-48.000MAAJ-T](#) [8Z-48.000MEEQ-T](#)