


0.020" $\pm$ 0.002" DIAMETER,
24 AWG, TINNED CCS,
1.0" LONG MINIMUM

GLASS BODY



RESISTANCE @ 25°C = 1,000,000 $\pm$ 5%
RESISTANCE/TEMPERATURE CURVE = "R"
BETA (0 TO +50°C) = 4,140°K NOMINAL
TEMPERATURE COEFFICIENT @ 25°C = -4.68%/°C NOMINAL
DISSIPATION CONSTANT = 2 mW/°C NOMINAL (STILL AIR)
THERMAL TIME CONSTANT = 5 SECONDS NOMINAL (STILL AIR)
THERMAL TIME COSNTANT = 0.5 SECONDS NOMINAL (STIRRED LIQUID)
MAXIMUM TEMPERATURE RATING = +300°C

---	ISO RELEASE	10/15/04	DD
"A"	LEAD WIRE WAS 0.020" $\pm$ 0.001" DIAMETER & 1.125" LONG NOMINAL	10/15/04	DD
REV	REVISION RECORD	DATE	APP

SCALE	NONE	U.S. SENSOR CORP. 1832 W. COLLINS AVE. ORANGE, CA 92867 714-639-1000 www.ussensor.com
DRAWN BY	R. DANKERT	
DATE	10/14/95	
REV.	"A"	
LAYER	0 OF 1	
		NTC THERMISTOR
		P/N 105RG1J