




Thick Film Resistor Networks, Military, MIL-PRF-83401 Qualified, Type RZ010 and RZ020 Dual-In-Line, Molded DIP



FEATURES

- Isolated, bussed and dual terminator schematics available
- MIL-PRF-83401 qualified
- Epoxy molded construction
- All device leads are hot-solder dipped
- Available in tube pack
- TCR available in "K" (± 100 ppm/ $^{\circ}$ C) or "M" (± 300 ppm/ $^{\circ}$ C) depending on style
- 100 % screen tested per group A, subgroup 1 of MIL-PRF-83401
- All devices are capable of passing the MIL-STD-202, method 210, condition D, "Resistance to Soldering Heat" test

| STANDARD ELECTRICAL SPECIFICATIONS | | | | | | | | | |
|------------------------------------|-----------|-----------------|-----------|---|---|---------------------------|----------------------------------|--|----------|
| VISHAY DALE MODEL/ PIN NO. | MIL STYLE | MIL SPEC. SHEET | SCHEMATIC | POWER RATING ELEMENT $P_{70^{\circ}\text{C}}$ W | POWER RATING PACKAGE $P_{70^{\circ}\text{C}}$ W | RESISTANCE RANGE Ω | TOLERANCE \pm % ⁽²⁾ | TEMPERATURE COEFFICIENT ⁽¹⁾ (-55 $^{\circ}$ C to +125 $^{\circ}$ C) \pm ppm/ $^{\circ}$ C | WEIGHT g |
| MDM14 | RZ010 | 01 | 01 (B) | 0.10 | 1.30 | 10 to 1M | 1, 2, 5 | 100, 300 | 1.3 |
| | | | 03 (A) | 0.20 | 1.40 | 10 to 1M | | | |
| | | | 05 (J) | 0.05 | 1.20 | Consult factory | | | |
| MDM16 | RZ020 | 02 | 01 (B) | 0.10 | 1.50 | 10 to 1M | 1, 2, 5 | 100, 300 | 1.5 |
| | | | 03 (A) | 0.20 | 1.60 | 10 to 1M | | | |
| | | | 05 (J) | 0.05 | 1.40 | Consult factory | | | |

Notes

- ⁽¹⁾ K = ± 100 ppm/ $^{\circ}$ C; M = ± 300 ppm/ $^{\circ}$ C
⁽²⁾ ± 2 % standard, ± 1 % and ± 5 % available


| GLOBAL PART NUMBER INFORMATION | | | | | | | | | | | | | | | | | |
|--|----------------------------|----------------------------|---|---|---|---|---|----------------------------|--|---|---|---|---|---|---|---|---|
| New Global Part Numbering: M8340101M2201GBD04 (preferred part numbering format) | | | | | | | | | | | | | | | | | |
| M | 8 | 3 | 4 | 0 | 1 | 0 | 1 | M | 2 | 2 | 0 | 1 | G | B | D | 0 | 4 |
| MIL STYLE | SPEC SHEET | CHARACTERISTIC | RESISTANCE VALUE | | | | TOLERANCE | SCHEMATIC | PACKAGING | | | | | | | | |
| M83401 | 01 = 14 pin 02 = 16 pin | K = 100 ppm M = 300 ppm | 3 digit significant figure, followed by a multiplier 10R0 = 10 Ω 3302 = 33 k Ω 1004 = 1 M Ω | | | | F = ± 1 % G = ± 2 % J = ± 5 % | A = Isolated B = Bussed | D04 = Tin/lead, tube DSL = Tin/lead, tube, single lot date code | | | | | | | | |
| Historical Part Number Example: M8340101M2201GB (will continue to be accepted) | | | | | | | | | | | | | | | | | |
| M83401 | 01 | M | 2201 | | | | G | B | D04 | | | | | | | | |
| MIL STYLE | SPEC SHEET | CHARACTERISTIC | RESISTANCE VALUE | | | | TOLERANCE | SCHEMATIC | PACKAGING | | | | | | | | |
| New Global Part Numbering: M8340102KA001GJD04 (preferred part numbering format) | | | | | | | | | | | | | | | | | |
| M | 8 | 3 | 4 | 0 | 1 | 0 | 2 | K | A | 0 | 0 | 1 | G | J | D | 0 | 4 |
| MIL STYLE | SPEC SHEET | CHARACTERISTIC | RESISTANCE VALUE | | | | TOLERANCE | SCHEMATIC | PACKAGING | | | | | | | | |
| M83401 | 01 = 14 pin 02 = 16 pin | K = 100 ppm M = 300 ppm | Per Std. MIL. Spec. (see Impedance Codes table) | | | | F = ± 1 % G = ± 2 % J = ± 5 % | J = Dual terminator | D04 = Tin/lead, tube DSL = Tin/lead, tube, single lot date code | | | | | | | | |
| Historical Part Number Example: M8340102KA001GJ (will continue to be accepted) | | | | | | | | | | | | | | | | | |
| M83401 | 02 | K | A001 | | | | G | J | D04 | | | | | | | | |
| MIL STYLE | SPEC SHEET | CHARACTERISTIC | RESISTANCE VALUE | | | | TOLERANCE | SCHEMATIC | PACKAGING | | | | | | | | |

Note

- For additional information on packaging, refer to the Through-Hole Network Packaging document (www.vishay.com/doc?31542).



DIMENSIONS in inches (millimeters)



| VISHAY DALE MODEL | A | B | C |
|-------------------|---------------|---------------|---|
| MDM14 | 0.750 (19.05) | 0.600 (15.24) | 6 |
| MDM16 | 0.850 (21.59) | 0.700 (17.78) | 7 |

| IMPEDANCE CODES | | | | | |
|-----------------|--------------------|--------------------|------|--------------------|--------------------|
| CODE | R ₁ (Ω) | R ₂ (Ω) | CODE | R ₁ (Ω) | R ₂ (Ω) |
| A001 | 82 | 130 | A010 | 330 | 470 |
| A002 | 120 | 200 | A011 | 330 | 680 |
| A003 | 130 | 210 | A012 | 1.5K | 3.3K |
| A004 | 160 | 260 | A013 | 3K | 6.2K |
| A005 | 180 | 240 | A014 | 180 | 270 |
| A006 | 180 | 390 | A015 | 270 | 270 |
| A007 | 220 | 270 | A016 | 560 | 560 |
| A008 | 220 | 330 | A017 | 560 | 1.2K |
| A009 | 330 | 390 | A018 | 620 | 2.7K |

| TECHNICAL SPECIFICATIONS | | |
|-----------------------------------|------------------|-------------|
| PARAMETER | UNIT | MDM SERIES |
| Maximum Operating Voltage | V _{DC} | 100 |
| Voltage Coefficient of Resistance | V _{eff} | < 50 ppm |
| Dielectric Strength | V _{AC} | 200 per min |
| Insulation Resistance | Ω | 10 000 M |
| Operating Temperature Range | °C | -55 to +125 |
| Storage Temperature Range | °C | -55 to +150 |


| MECHANICAL SPECIFICATIONS | |
|--------------------------------|--------------------------------------|
| Marking Resistance to Solvents | Permanency testing per MIL-PRF-83401 |
| Solderability | Per MIL-PRF-83401 |
| Body | Molded epoxy |
| Terminals | Copper alloy, hot-solder dipped |

| CIRCUIT APPLICATIONS | |
|----------------------------|---|
| <p>01 Schematic</p> | <p>MDM1401 (M8340101xxxxxB) MDM1601 (M8340102xxxxxB)</p> <p>13 or 15 resistors with one pin common</p> <p>The MDMxx01 provides the user with a choice of 13 or 15 nominally equal resistors, each connected to a common pin. Commonly used in the following applications:</p> <ul style="list-style-type: none"> • MOS/ROM Pull-up/Pull-down • Open Collector Pull-up • “Wired OR” Pull-up • Power Driven Pull-up • TTL Input Pull-down • Digital Pulse Squaring • TTL Unused Gate Pull-up • High Speed Parallel Pull-up |
| <p>03 Schematic</p> | <p>MDM1403 (M8340101xxxxxA) MDM1603 (M8340102xxxxxA)</p> <p>7 or 8 isolated resistors</p> <p>The MDMxx03 provides the user with a choice of 7 or 8 nominally equal resistors, with each resistor isolated from all others. Commonly used in the following applications:</p> <ul style="list-style-type: none"> • “Wired OR” Pull-up • Power Driven Pull-up • Power Gate Pull-up • Line Termination • Long-line Impedance Balancing • LED Current Limiting • ECL Output Pull-down • TTL Input Pull-down |
| <p>05 Schematic</p> | <p>MDM1405 (M8340101xxxxxJ) MDM1605 (M8340102xxxxxJ)</p> <p>12 or 14 resistor pairs</p> <p>The MDMxx05 provides the user with a choice of 12 or 14 pairs of R1/R2 resistor values for pulse squaring and TTL dual-line terminating requirements.</p> |


CAGE CODE: 91637

DERATING


01 Schematic



03 Schematic



05 Schematic





| PERFORMANCE | | |
|---------------------------------|---|--|
| TEST | CONDITIONS | MAX. ΔR (TYPICAL TEST LOTS) |
| Power Conditioning | 1.5 x rated power, applied 1.5 h "ON" and 0.5 h "OFF" for 100 h ± 4 h at +25 °C ambient temperature | ± 0.50 % ΔR |
| Thermal Shock | 5 cycles between -65 °C and +125 °C | ± 0.50 % ΔR |
| Short Time Overload | 2.5 x rated working voltage for 5 s | ± 0.25 % ΔR (Char. K) ± 0.50 % ΔR (Char. M) |
| Low Temperature Operation | 45 min at full rated working voltage at -65 °C | ± 0.25 % ΔR (Char. K) ± 0.50 % ΔR (Char. M) |
| Moisture Resistance | 240 h with humidity ranging from 80 % RH to 98 % RH | ± 0.50 % ΔR |
| Resistance to Soldering Heat | Leads immersed in +260 °C solder to within 1/16" of body for 10 s | ± 0.25 % ΔR |
| Shock | Total of 18 shocks at 100 g's | ± 0.25 % ΔR |
| Vibration | 12 h at maximum of 20 g's between 10 Hz and 2000 Hz | ± 0.25 % ΔR |
| Load Life | 1000 h at +70 °C, rated power applied 1.5 h "ON", 0.5 h "OFF" for full 1000 h period | ± 0.50 % ΔR (Char. K) ± 2.00 % ΔR (Char. M) |
| Terminal Strength | 4.5 pound pull for 30 s | ± 0.25 % ΔR |
| Insulation Resistance | 10 000 MΩ (minimum) | - |
| Dielectric Withstanding Voltage | No evidence of arcing or damage (200 V _{RMS} for 1 min) | - |



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.