


Bulk Metal® Foil Technology High Precision 4-Terminal Power Current Sensing Resistors with TCR as low as $\pm 1 \text{ ppm}/^\circ\text{C}$ Maximum, Tolerance $\pm 0.1 \%$ and Rise Time 1.0 ns Effectively No Ringing



INTRODUCTION

The VCS331 and VCS332 offer precision Bulk Metal® Foil technology resistors as low as 0.25Ω with a temperature coefficient down to $1 \text{ ppm}/^\circ\text{C}$ maximum and unmatched long term stability. The 4 terminal current sensing resistors, when mounted on a heat sink, can sustain 10 W continuously without an appreciable change in resistance (0.15% maximum). The typical 50% power derating specification associated with other technologies is not necessary. A choice of lead configurations is available.

Our application engineering department is available to advise and make recommendations. For non-standard technical requirements and special applications, please contact us.

FEATURES

- Temperature coefficient of resistance (TCR): down to $\pm 1 \text{ ppm}/^\circ\text{C}$ max. (see table 2)
- Tolerance: to $\pm 0.1 \%$ (see table 1)
- Power rating (heat-sinked): 10 W
- Load life stability: $\pm 0.01 \%$ (100 ppm) at 25°C , 2000 h at rated power
- Resistance range: 0.25Ω to 500Ω
- Vishay Foil resistors are not restricted to standard values; specific "as required" values can be supplied at no extra cost or delivery (e.g. 1R2345 vs. 1R)
- Electrostatic discharge (ESD) up to 25 000 V
- Non-inductive, non-capacitive design
- Rise time: 1.0 ns effectively no ringing
- Current noise: $0.010 \mu\text{V}_{\text{RMS}}/\text{V}$ of applied voltage ($< -40 \text{ dB}$)
- Thermal EMF: $0.05 \mu\text{V}/^\circ\text{C}$ typical
- Voltage coefficient: $< 0.1 \text{ ppm}/\text{V}$
- Non-inductive: $0.08 \mu\text{H}$
- Non hot spot design
- Thermal stabilization time $< 1 \text{ s}$ (nominal value achieved within 10 ppm of steady state value)
- Terminal finish: lead (Pb)-free or tin/lead alloy
- Prototype quantities available in just 5 working days or sooner. For more information, please contact foil@vishaypg.com
- For better performances, please contact application engineering



RoHS*
COMPLIANT

TABLE 1 - CHARACTERISTICS

MODEL NUMBER	RESISTANCE RANGE	BEST TOLERANCE (1)	POWER RATING (2) at $+25^\circ\text{C}$	MAXIMUM CURRENT (2)
VCS331, VCS332	$0.25 \Omega < R < 500 \Omega$	$\pm 0.1 \%$	10 W on heat sink (3) or 3 W in free air	5 A

Notes

(1) Tighter tolerance is available - for more details contact application engineering


(2) The lower of the two limitations (power or current) is decisive

(3) Heatsink - aluminum (6" length x 4" width x 2" height x 0.04" thick)

TABLE 2 - TCR CHART (maximum)

(0 $^\circ\text{C}$ TO $+60^\circ\text{C}$)		
$\geq 0.25 \Omega$	to $< 1 \Omega$	$\pm 3 \text{ ppm}/^\circ\text{C}$
$\geq 1 \Omega$	to $< 10 \Omega$	$\pm 2 \text{ ppm}/^\circ\text{C}$
$\geq 10 \Omega$	to $< 500 \Omega$	$\pm 1 \text{ ppm}/^\circ\text{C}$


FIGURE 1 - POWER DERATING CURVE



* Pb containing materials are not RoHS compliant, exemptions may apply

FIGURE 2 - TRIMMING TO VALUES

(conceptual illustration)




Note: Foil shown in black, etched spaces in white

FIGURE 3- DIMENSIONS in inches (millimeters) **AND SCHEMATIC**

Model VCS331 (E Lead Rectangular)

Model VCS332 (Round Leads)



MODEL	L_1 ± 0.008 (± 0.20)	L_2 ± 0.008 (± 0.20)	H_1 MAX.	H_2 ± 0.008 (± 0.20)	W_1 MAX.	W_2 MAX.	LL MIN.	LS ± 0.020 (± 0.51)	LT ± 0.020 (± 0.51)	D_1 NOM.	D_2 NOM.	P NOM.	T NOM.
VCS331	1.340 (34.04)	0.701 (17.81)	1.063 (27.00)	0.197 (5.00)	0.210 (5.33)	0.087 (2.21)	0.216 (5.49)	0.689 (17.50)	1.083 (27.51)	0.138 (3.51)	0.040 (1.02)	0.040 (1.02)	0.016 (0.41)
VCS332	1.340 (34.04)	0.701 (17.81)	1.024 (26.01)	0.197 (5.00)	0.210 (5.33)	0.087 (2.21)	1.000 (25.40)	0.689 (17.50)	1.083 (27.51)	0.138 (3.51)	0.040 (1.02)	0.032 (0.81)	-

TABLE 3 - VISHAY VCS331, VCS332 PERFORMANCE


TEST OR CONDITION	VCS331, VCS332 PERFORMANCE ⁽¹⁾	
	TYPICAL ΔR LIMITS	MAXIMUM ΔR LIMITS
Thermal Shock	0.01 %	0.02 %
Short Time Overload (5 x rated power for 5 s)	0.01 %	0.02 %
Terminal Strength	0.02 %	0.05 %
High Temperature Exposure (2000 h at + 150 °C)	0.02 %	0.05 %
Moisture Resistance	0.03 %	0.05 %
Low Temperature Storage (24 h at - 55 °C)	0.005 %	0.01 %
Shock (specified pulse)	0.01 %	0.02 %
Vibration (high frequency)	0.01 %	0.02 %
Load Life (rated power, + 25 °C, 2000 h)	0.01 %	0.02 %
Resistance Tolerance	0.1 %	1 %
Thermal EMF	0.2 $\mu V/^{\circ}C$ max. (E terminal)	
Weight	8.1 g maximum	

Notes

⁽¹⁾ ΔR 's plus additional 0.0005 Ω for measurement error

TABLE 4 - GLOBAL PART NUMBER INFORMATION ⁽¹⁾


NEW GLOBAL PART NUMBER: Y09600R25000B9L (preferred part number format)



FOR EXAMPLE: ABOVE GLOBAL ORDER Y0960 0R25000 B 9 L:

TYPE: VCS331
VALUE: 0.25 Ω
ABSOLUTE TOLERANCE: $\pm 0.1\%$
TERMINATION: lead (Pb)-free
PACKAGING: bulk

HISTORICAL PART NUMBER: VCS331T 0R2500 B B (will continue to be used)


Note

⁽¹⁾ For non-standard requests, please contact application engineering

Disclaimer

ALL PRODUCTS, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Vishay Precision Group, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "VPG"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

The product specifications do not expand or otherwise modify VPG's terms and conditions of purchase, including but not limited to, the warranty expressed therein.

VPG makes no warranty, representation or guarantee other than as set forth in the terms and conditions of purchase.

To the maximum extent permitted by applicable law, VPG disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Information provided in datasheets and/or specifications may vary from actual results in different applications and performance may vary over time. Statements regarding the suitability of products for certain types of applications are based on VPG's knowledge of typical requirements that are often placed on VPG products. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. You should ensure you have the current version of the relevant information by contacting VPG prior to performing installation or use of the product, such as on our website at vpgsensors.com.

No license, express, implied, or otherwise, to any intellectual property rights is granted by this document, or by any conduct of VPG.

The products shown herein are not designed for use in life-saving or life-sustaining applications unless otherwise expressly indicated. Customers using or selling VPG products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify VPG for any damages arising or resulting from such use or sale. Please contact authorized VPG personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.

Copyright Vishay Precision Group, Inc., 2014. All rights reserved.