

HDC enclosures
HDC 48A SDLU 1PG29G

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

Type	HDC 48A SDLU 1PG29G
Order No.	1666810000
Version	HDC enclosures, Size: 9, Protection degree: IP 65, Base enclosure, End-locking clamp, lower side, Standard, with cover, Size of cable entries: PG 29
GTIN (EAN)	4008190423926
Qty.	1 pc(s).

HDC enclosures HDC 48A SDLU 1PG29G

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Length	126 mm	Width	143.1 mm
Height	96 mm	Mounting dimension - width	112 mm
Mounting dimension - height	67 mm	Net weight	845 g

Dimensions

Total length housing	94 mm	Width housing C	82.5 mm
Width base C1	92.5 mm	Height of housing B	96 mm
Height of base B1	5 mm	Hole pitch length A2	112 mm
Cable entry	w. threading		

General data

Protection class note	Protection class with secured cover: IP 65	Housing main material	diecast aluminium
-----------------------	--	-----------------------	-------------------

Version

Internal thread	PG 29	Design of housing	Base enclosure
Size	9	Design	Standard
Top part/bottom part/lid	lower part	Design of locking system	End-locking clamp, lower side
Cable entry	w. threading	Size of cable entries	PG 29
Number of cable entry on top	0	Number of cable entry sideways	1
Cover	with cover	Design of cover	with cover

Classifications

ETIM 2.0	EC000437	ETIM 3.0	EC000437
UNSPSC	30-21-18-01	eClass 4.1	27-14-08-05
eClass 5.1	27-14-34-19	eClass 6.2	27-26-12-03
eClass 7.1	27-44-02-02		

Approvals

Approvals



ROHS

Conform

Downloads

PDF	1666810000_HDC_48A_SDLU_1PG29G_STP_Blatt_1.pdf
IGES	1666810000_HDC_48A_SDLU_1PG29G_STP.igs
VRML	1666810000_HDC_48A_SDLU_1PG29G_STP.wrl
EPLAN	1666810000.MZF
3-D model	