

Pitch 3.81 mm (0.150 inch)
SC-SMT 3.81/04/180G 3.2SN BK BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-2083
 www.weidmueller.com



High-temperature-resistant pin header (SC-SMT 180G) in 3.81-mm pitch (0.15 inch)

- Plugging direction is perpendicular to PCB (standing)
- Closed (G) .
- Packed either in box (BX) or on anti-static roll (tape-on-reel, RL)
- Pin length of either 1.5 mm or 3.2 mm

Weidmüller's 3.81-mm-pitch (0.15 inch) plug-in connectors are compatible with the layouts of standard connectors and offer space for labelling and coding.

- 320 V (IEC) / 300 V (UL)
- 14.9 A (IEC) / 10 A (UL)

General ordering data

Order No.	1862950000
Part designation	SC-SMT 3.81/04/180G 3.2SN BK BX
Version	PCB plug-in connector, male header, 3.81 mm, No. of poles: 4, 180°, Solder pin length: 3.2 mm, tinned, black, Reflow solder connection, Box
GTIN (EAN)	4032248428137
Qty.	50 pc(s).
Packaging	Box

Pitch 3.81 mm (0.150 inch) SC-SMT 3.81/04/180G 3.2SN BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-2083
www.weidmueller.com

Technical data

System parameters

Fitted to PCB	Reflow solder connection	Outgoing elbow	180°
Pitch in mm	3.81 mm	Pitch in inch	0.15 inch
No. of poles	4	Solder pin length	3.2 mm
Can be coded	Yes	No. of rows	1
Number of solder pins per pole	1	Diameter of solder eyelet	1.3 mm
Tolerance of the diameter of the solder eyelet	+ 0,1 mm	L1 in mm	11.43 mm
L1 in inch	0.45 inch	Insulation resistance	10 ³ Ω
Electric shock protection to DIN VDE 0470	IP 20	Electric shock protection to DIN VDE 57 106	Safe from finger touch

Material data

Insulating material	LCP GF	Colour	black
Insulating material group	IIIa	Flammability class UL 94	V-0
CTI	≥ 175	Contact material	Copper alloy
Contact surface	tinned	Highest continuous operating temperature, min.	-25 °C
Highest continuous operating temperature, max.	120 °C	Max. relative humidity during storage	85 %

DIN IEC rating data

Rated current, min. No. of poles (Tu=20°C)	17.5 A	Rated current, max. No. of poles (Tu=20°C)	13.9 A
Rated current, no. of poles (Tu=40°C), min.	17 A	Rated current, no. of poles (Tu=40°C), max.	12.4 A
Rated voltage at overvoltage category/pollution degree III/3	160 V	Rated impulse withstand voltage for overvoltage class/pollution severity III/3	2.5 kV
Rated voltage for overvoltage class/pollution severity III/2	160 V	Rated impulse withstand voltage for overvoltage class/pollution severity III/2	2.5 kV
Rated voltage for overvoltage class/pollution severity II/2	320 V	Rated impulse withstand voltage for overvoltage class/pollution severity II/2	2.5 kV
Short-time withstand current resistance	3 x 1s with 76 A		

CSA rating data

Rated voltage (Use group B)	300 V	Rated current (use group B)	10 A
Rated voltage (use group D)	300 V	Rated current (use group D)	10 A

UL 1059 rating data

Rated voltage (use group B)	300 V	Rated current (use group B)	10 A
Rated voltage (use group D)	300 V	Rated current (use group D)	10 A

Approvals

Approvals institutes	CSA; CURUS; ROHS
----------------------	------------------

Classifications

ETIM 3.0	EC001284	eClass 5.1	27-26-07-04
eClass 6.0	27-26-07-04		

Pitch 3.81 mm (0.150 inch)
SC-SMT 3.81/04/180G 3.2SN BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-2083
www.weidmueller.com

Technical data

Notes


Notes

- Additional colours on request
- Rated current related to rated cross-section and min. No. of poles.
- P on drg. = pitch
- Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.

Pitch 3.81 mm (0.150 inch)
SC-SMT 3.81/04/180G 3.2SN BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-2083
www.weidmueller.com

Drawings



Pitch 3.81 mm (0.150 inch)
SC-SMT 3.81/04/180G 3.2SN BK BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-2083
 www.weidmueller.com

Counterpart

BCZ 3.81/180



Female socket connectors with clamping-yoke screw system for connecting wires.

Three wire-outlet directions are available and provide flexible connection-level design options:

- 180° wire parallel to plugging direction
- 90° wire perpendicular and above plugging direction
- 270° wire perpendicular and below plugging direction

There are three housing shapes, covering many different requirements, to choose from:

- Standard housing without flange
 - Flange with screw (F)
 - Flange featuring Weidmüller's patented release latch (LR) for lock-and-release latching with no strain and no tools needed.
- Weidmüller's 3.81-mm-pitch (0.15 inch) plug-in connectors are compatible with the layouts of customary connectors and offer space for labelling and coding.
- 0.20 - 1.5 mm² (IEC) / 28 - 16 AWG (UL)
 - 250 V (IEC) / 300 V (UL)
 - 17.5 A (IEC) / 10 A (UL)

General ordering data

Order No.	Part designation	Version	GTIN (EAN)	Qty.	Packaging
1940750000	BCZ 3.81/04/180 SN OR BX	PCB plug-in connector, female plug, 3.81 mm, No. of poles: 4, 180°, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Box	4032248656080	50 pc(s).	Box
1792880000	BCZ 3.81/04/180 SN GN BX	PCB plug-in connector, female plug, 3.81 mm, No. of poles: 4, 180°, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Box	4032248226962	50 pc(s).	Box
1792790000	BCZ 3.81/04/180 SN BK BX	PCB plug-in connector, female plug, 3.81 mm, No. of poles: 4, 180°, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Box	4032248226771	50 pc(s).	Box

Pitch 3.81 mm (0.150 inch)
SC-SMT 3.81/04/180G 3.2SN BK BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-2083
 www.weidmueller.com

Counterpart

BCZ 3.81/270



Female socket connectors with clamping-yoke screw system for connecting wires.

Three wire-outlet directions are available and provide flexible connection-level design options:

- 180° wire parallel to plugging direction
- 90° wire perpendicular and above plugging direction
- 270° wire perpendicular and below plugging direction

There are three housing shapes, covering many different requirements, to choose from:

- Standard housing without flange
 - Flange with screw (F)
 - Flange featuring Weidmüller's patented release latch (LR) for lock-and-release latching with no strain and no tools needed.
- Weidmüller's 3.81-mm-pitch (0.15 inch) plug-in connectors are compatible with the layouts of customary connectors and offer space for labelling and coding.
- 0.20 - 1.5 mm² (IEC) / 28 - 16 AWG (UL)
 - 250 V (IEC) / 300 V (UL)
 - 17.5 A (IEC) / 10 A (UL)

General ordering data

Order No.	Part designation	Version	GTIN (EAN)	Qty.	Packaging
1798950000	BCZ 3.81/04/270 SN BK BX	PCB plug-in connector, female plug, 3.81 mm, No. of poles: 4, 270°, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Box	4032248243730	50 pc(s).	Box
1940210000	BCZ 3.81/04/270 SN OR BX	PCB plug-in connector, female plug, 3.81 mm, No. of poles: 4, 270°, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Box	4032248656622	50 pc(s).	Box
1799030000	BCZ 3.81/04/270 SN GN BX	PCB plug-in connector, female plug, 3.81 mm, No. of poles: 4, 270°, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Box	4032248243921	50 pc(s).	Box

Pitch 3.81 mm (0.150 inch)
SC-SMT 3.81/04/180G 3.2SN BK BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-2083
 www.weidmueller.com

Counterpart

BCZ 3.81/90



Female socket connectors with clamping-yoke screw system for connecting wires.

Three wire-outlet directions are available and provide flexible connection-level design options:

- 180° wire parallel to plugging direction
- 90° wire perpendicular and above plugging direction
- 270° wire perpendicular and below plugging direction

There are three housing shapes, covering many different requirements, to choose from:

- Standard housing without flange
 - Flange with screw (F)
 - Flange featuring Weidmüller's patented release latch (LR) for lock-and-release latching with no strain and no tools needed.
- Weidmüller's 3.81-mm-pitch (0.15 inch) plug-in connectors are compatible with the layouts of customary connectors and offer space for labelling and coding.
- 0.20 - 1.5 mm² (IEC) / 28 - 16 AWG (UL)
 - 250 V (IEC) / 300 V (UL)
 - 17.5 A (IEC) / 10 A (UL)

General ordering data

Order No.	Part designation	Version	GTIN (EAN)	Qty.	Packaging
1939840000	BCZ 3.81/04/90 SN OR BX	PCB plug-in connector, female plug, 3.81 mm, No. of poles: 4, 90°, Clamping yoke connection, Clamping range, max.: 1.5 mm², Box	4032248653942	50 pc(s).	Box
1798710000	BCZ 3.81/04/90 SN GN BX	PCB plug-in connector, female plug, 3.81 mm, No. of poles: 4, 90°, Clamping yoke connection, Clamping range, max.: 1.5 mm², Box	4032248243297	50 pc(s).	Box
1798550000	BCZ 3.81/04/90 SN BK BX	PCB plug-in connector, female plug, 3.81 mm, No. of poles: 4, 90°, Clamping yoke connection, Clamping range, max.: 1.5 mm², Box	4032248243211	50 pc(s).	Box

Pitch 3.81 mm (0.150 inch)
SC-SMT 3.81/04/180G 3.2SN BK BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-2083
 www.weidmueller.com

Counterpart

BCZ 3.81/180F



Female socket connectors with clamping-yoke screw system for connecting wires.

Three wire-outlet directions are available and provide flexible connection-level design options:

- 180° wire parallel to plugging direction
- 90° wire perpendicular and above plugging direction
- 270° wire perpendicular and below plugging direction

There are three housing shapes, covering many different requirements, to choose from:

- Standard housing without flange
 - Flange with screw (F)
 - Flange featuring Weidmüller's patented release latch (LR) for lock-and-release latching with no strain and no tools needed.
- Weidmüller's 3.81-mm-pitch (0.15 inch) plug-in connectors are compatible with the layouts of customary connectors and offer space for labelling and coding.
- 0.20 - 1.5 mm² (IEC) / 28 - 16 AWG (UL)
 - 250 V (IEC) / 300 V (UL)
 - 17.5 A (IEC) / 10 A (UL)

General ordering data

Order No.	Part designation	Version	GTIN (EAN)	Qty.	Packaging
1793060000	BCZ 3.81/04/180F SN GN BX	PCB plug-in connector, female plug, 3.81 mm, No. of poles: 4, 180°, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Box	4032248227143	50 pc(s).	Box
1941030000	BCZ 3.81/04/180F SN OR BX	PCB plug-in connector, female plug, 3.81 mm, No. of poles: 4, 180°, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Box	4032248655816	50 pc(s).	Box
1792970000	BCZ 3.81/04/180F SN BK BX	PCB plug-in connector, female plug, 3.81 mm, No. of poles: 4, 180°, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Box	4032248227051	50 pc(s).	Box

Pitch 3.81 mm (0.150 inch)
SC-SMT 3.81/04/180G 3.2SN BK BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-2083
 www.weidmueller.com

Counterpart

BCZ 3.81/270F



Female socket connectors with clamping-yoke screw system for connecting wires.

Three wire-outlet directions are available and provide flexible connection-level design options:

- 180° wire parallel to plugging direction
- 90° wire perpendicular and above plugging direction
- 270° wire perpendicular and below plugging direction

There are three housing shapes, covering many different requirements, to choose from:

- Standard housing without flange
 - Flange with screw (F)
 - Flange featuring Weidmüller's patented release latch (LR) for lock-and-release latching with no strain and no tools needed.
- Weidmüller's 3.81-mm-pitch (0.15 inch) plug-in connectors are compatible with the layouts of customary connectors and offer space for labelling and coding.
- 0.20 - 1.5 mm² (IEC) / 28 - 16 AWG (UL)
 - 250 V (IEC) / 300 V (UL)
 - 17.5 A (IEC) / 10 A (UL)

General ordering data

Order No.	Part designation	Version	GTIN (EAN)	Qty.	Packaging
1799190000	BCZ 3.81/04/270F SN GN BX	PCB plug-in connector, female plug, 3.81 mm, No. of poles: 4, 270°, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Box	4032248244089	50 pc(s).	Box
1799110000	BCZ 3.81/04/270F SN BK BX	PCB plug-in connector, female plug, 3.81 mm, No. of poles: 4, 270°, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Box	4032248244003	50 pc(s).	Box
1940480000	BCZ 3.81/04/270F SN OR BX	PCB plug-in connector, female plug, 3.81 mm, No. of poles: 4, 270°, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Box	4032248656356	50 pc(s).	Box

Pitch 3.81 mm (0.150 inch)
SC-SMT 3.81/04/180G 3.2SN BK BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-2083
 www.weidmueller.com

Counterpart

BCZ 3.81/90F



Female socket connectors with clamping-yoke screw system for connecting wires.

Three wire-outlet directions are available and provide flexible connection-level design options:

- 180° wire parallel to plugging direction
- 90° wire perpendicular and above plugging direction
- 270° wire perpendicular and below plugging direction

There are three housing shapes, covering many different requirements, to choose from:

- Standard housing without flange
 - Flange with screw (F)
 - Flange featuring Weidmüller's patented release latch (LR) for lock-and-release latching with no strain and no tools needed.
- Weidmüller's 3.81-mm-pitch (0.15 inch) plug-in connectors are compatible with the layouts of customary connectors and offer space for labelling and coding.
- 0.20 - 1.5 mm² (IEC) / 28 - 16 AWG (UL)
 - 250 V (IEC) / 300 V (UL)
 - 17.5 A (IEC) / 10 A (UL)

General ordering data

Order No.	Part designation	Version	GTIN (EAN)	Qty.	Packaging
1798790000	BCZ 3.81/04/90F SN BK BX	PCB plug-in connector, female plug, 3.81 mm, No. of poles: 4, 90°, Clamping yoke connection, Clamping range, max.: 1.5 mm², Box	4032248243471	50 pc(s).	Box
1940000000	BCZ 3.81/04/90F SN OR BX	PCB plug-in connector, female plug, 3.81 mm, No. of poles: 4, 90°, Clamping yoke connection, Clamping range, max.: 1.5 mm², Box	4032248656820	50 pc(s).	Box
1798870000	BCZ 3.81/04/90F SN GN BX	PCB plug-in connector, female plug, 3.81 mm, No. of poles: 4, 90°, Clamping yoke connection, Clamping range, max.: 1.5 mm², Box	4032248243556	50 pc(s).	Box

Pitch 3.81 mm (0.150 inch)
SC-SMT 3.81/04/180G 3.2SN BK BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-2083
 www.weidmueller.com

Counterpart

BCZ 3.81/180LR



Female socket connectors with clamping-yoke screw system for connecting wires.

Three wire-outlet directions are available and provide flexible connection-level design options:

- 180° wire parallel to plugging direction
- 90° wire perpendicular and above plugging direction
- 270° wire perpendicular and below plugging direction

There are three housing shapes, covering many different requirements, to choose from:

- Standard housing without flange
 - Flange with screw (F)
 - Flange featuring Weidmüller's patented release latch (LR) for lock-and-release latching with no strain and no tools needed.
- Weidmüller's 3.81-mm-pitch (0.15 inch) plug-in connectors are compatible with the layouts of customary connectors and offer space for labelling and coding.
- 0.20 - 1.5 mm² (IEC) / 28 - 16 AWG (UL)
 - 250 V (IEC) / 300 V (UL)
 - 17.5 A (IEC) / 10 A (UL)

General ordering data

Order No.	Part designation	Version	GTIN (EAN)	Qty.	Packaging
1941420000	BCZ 3.81/04/180LR SN OR BX	PCB plug-in connector, female plug, 3.81 mm, No. of poles: 4, 180°, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Box	4032248698349	50 pc(s).	Box
1941800000	BCZ 3.81/04/180LR SN BK BX	PCB plug-in connector, female plug, 3.81 mm, No. of poles: 4, 180°, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Box	4032248698721	50 pc(s).	Box
1941610000	BCZ 3.81/04/180LR SN GN BX	PCB plug-in connector, female plug, 3.81 mm, No. of poles: 4, 180°, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Box	4032248698530	50 pc(s).	Box