

SAI Active SAI-AU M12 IE GW 16DI

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com



Many gateway I/O units are available. Choose between PROFIBUS-DP, DeviceNet, USB and the Ethernet dialects EtherNet/IP, Modbus TCP and PROFINET IO. The gateways have 16 digital inputs, the USB modul has 8 additional outputs. The USB is connected to the PC via a USB port, it operates at every USB port after the driver has been installed. Implementation via the simple Modbus standard protocol is possible.

General ordering data

Type	SAI-AU M12 IE GW 16DI
Order No.	1938580000
Version	SAI Active, Modbus TCP, Complete modul
GTIN (EAN)	4032248612390
Qty.	1 pc(s).

SAI Active
SAI-AU M12 IE GW 16DI

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Length	210 mm	Width	54 mm
Height	32 mm	Net weight	999 g

Configuration

System integration	Register, Webserver
--------------------	---------------------

Connections

Connection to Subbus (SUB-OUT)	1 x M8 female 4-pole, A-coded	Fieldbus (BUS-IN)	1 x M12 female 4-pole, D-coded
I/O connections	8 x M12 socket 5-pole, A-coded	Supply voltage (AUX-IN)	1 x M12 plug 5-pole, A-coded

Digital inputs

Input current, high	2 mA to 15 mA in accordance with EN 61131-2 Type 1	Input current, low	< 15 mA in accordance with EN 61131-2 Type 1
Input filter	1 ms, 3 ms, 5 ms, 10 ms, configurable	Input voltage, high	>15 V in accordance with EN 61131-2 Type 1
Input voltage, low	<5 V in accordance with EN 61131-2 Type 1	Permitted input voltage	-30 V to +30 V (protected against polarity reversal)
Separation of potentials to module electronics [digital inputs]	none		

General data

Certificate	CE, cULus	Earth	< 350 g
Housing main material	Pocan, PBT	Protection degree	IP 67
UL 94 flammability rating	V-0		

Fieldbus

Addressing	DHCP, BOOTP, Static	Bus system	Modbus TCP
Transmission rate	10/100 Mbit/s		

Functional inputs

Input filter	1 ms, 3 ms, 5 ms, 10 ms, configurable
--------------	---------------------------------------

Supply voltage

Contact load	Per PIN max. 4 A	Limits	18 V DC ... 30 V DC
Max. total current module	8 A	Operating voltage	24 V
Reverse polarity protection	Yes		

Classifications

ETIM 3.0	EC001597	UNSPSC	43-17-27-10
eClass 5.1	27-25-04-03	eClass 6.2	27-24-26-04
eClass 7.1	27-24-26-04		

Data sheet...

SAI Active
SAI-AU M12 IE GW 16DI

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Approvals

Approvals



ROHS

Conform