

# 140 Watts

## ECM Series



- 120/148 W – Convection/Forced-cooled Ratings
- Class I & Class II Construction
- Remote Sense
- 5 V Standby Option
- Remote On/Off & Power OK Signals Option
- IT, Industrial & Medical Safety Approvals
- 3 Year Warranty

### Specification

#### Input

|                       |                                                                              |
|-----------------------|------------------------------------------------------------------------------|
| Input Voltage         | • 80-264 VAC (120-370 VDC), derate output power <90 VAC (See derating curve) |
| Input Frequency       | • 47-400 Hz <sup>(1)</sup>                                                   |
| Input Current         | • 2.5 A typical at 115 VAC, full load<br>1.3 A typical at 230 VAC, full load |
| Inrush Current        | • 40 A max at 230 VAC, cold start at 25 °C                                   |
| Power Factor          | • EN61000-3-2, class A                                                       |
| Earth Leakage Current | • 265 µA max at 264 VAC/60 Hz<br>0.5/1.1 mA 115/230 VAC at 400 Hz typ.       |
| Input Protection      | • Internal T5.0 A/250 V fuse in line and neutral                             |

#### Output

|                                          |                                                                                  |
|------------------------------------------|----------------------------------------------------------------------------------|
| Output Voltage                           | • 12-48 VDC (see tables)                                                         |
| Output Voltage Trim                      | • ±5%, fan output will track by same percentage                                  |
| Initial Set Accuracy                     | • ±1% V1, ±5% V2, ±3% V3                                                         |
| Minimum Load                             | • 0.1 A required on V1 to maintain regulation of V2                              |
| Start Up Delay                           | • 1.5 s max                                                                      |
| Start Up Rise Time                       | • 10 ms max                                                                      |
| Hold Up Time                             | • 16 ms min at 115 VAC                                                           |
| Drift                                    | • ±0.2% after 20 min warm up                                                     |
| Line Regulation                          | • ±0.5% max                                                                      |
| Load Regulation                          | • ±1% V1, ±5% V2 & V3 max                                                        |
| Over/Undershoot                          | • 5% typical                                                                     |
| Transient Response                       | • 4% max. deviation, recovery to within 1% in 500 µs for a 50-75-50% load change |
| Ripple & Noise                           | • 1% pk-pk V1, others 2%, 20 MHz bandwidth                                       |
| Overvoltage Protection                   | • 115-140% Vnom, recycle input to reset                                          |
| Overload Protection                      | • 110-150% V1 only                                                               |
| Short Circuit Protection                 | • Continuous trip and restart (hiccup mode)                                      |
| Temperature Coefficient                  | • 0.05%/°C                                                                       |
| Remote Sense                             | • Compensates for 0.5 V total voltage drop                                       |
| Remote On/Off (Inhibit/Enable Option -A) | • Uncommitted isolated optocoupler diode, powered diode inhibits V1 & V2         |

#### General

|                     |                                                                                                  |
|---------------------|--------------------------------------------------------------------------------------------------|
| Efficiency          | • 88% typical                                                                                    |
| Isolation           | • 4000 VAC Input to Output 2 x MOPP, 1500 VAC Input to Ground 1 x MOPP, 500 VAC Output to Ground |
| Switching Frequency | • 70 kHz typical                                                                                 |
| Signals (Option -A) | • Power OK - open collector, Remote On/Off, 5 V Standby                                          |
| MTBF                | • 220 kHrs to MIL-HDBK-217F at 25 °C, GB                                                         |
| Power Density       | • 7.2 W/in <sup>3</sup>                                                                          |

#### Environmental

|                       |                                                                                                                                                                                               |
|-----------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Operating Temperature | • 0 °C to +70 °C derate linearly from +50 °C at 2.5%/°C to 50% load at +70 °C when convection-cooled and from +60 °C at 2.5%/°C to 75% load at +70 °C when forced-cooled. See derating curve. |
| Cooling               | • Convection & fan cooled ratings (see tables)                                                                                                                                                |
| Operating Humidity    | • 95% RH, non-condensing                                                                                                                                                                      |
| Storage Temperature   | • -40 °C to +85 °C                                                                                                                                                                            |
| Operating Altitude    | • 3000 m                                                                                                                                                                                      |
| Shock                 | • 30 g pk, half sine, 6 axes                                                                                                                                                                  |
| Vibration             | • 2 g rms, 5 Hz to 500 Hz, 3 axes                                                                                                                                                             |

#### EMC & Safety

|                               |                                                                                                                                                                                     |
|-------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Low Voltage PSU EMC Emissions | • EN61204-3, high severity level<br>• EN55011/22 level B conducted<br>EN55011/22 level A radiated                                                                                   |
| Harmonic Currents             | • EN61000-3-2, class A                                                                                                                                                              |
| Voltage Flicker               | • EN61000-3-3                                                                                                                                                                       |
| Radiated Immunity             | • EN61000-4-3, level 3 Perf Criteria A                                                                                                                                              |
| EFT/Burst                     | • EN61000-4-4, level 3 Perf Criteria A                                                                                                                                              |
| Surge                         | • EN61000-4-5, installation class 3 Perf Criteria A                                                                                                                                 |
| Conducted Immunity            | • EN61000-4-6, level 3 Perf Criteria A                                                                                                                                              |
| Dips & Interruptions          | • EN61000-4-11, 30% 10 ms, 60% 100 ms, 100% 5000 ms, Perf Criteria A, B, B<br>EN60601-1, 30% 500 ms, 60% 100 ms, 100% 10 ms, 100% 5000 ms, Perf Criteria A, A (with 50% load), A, B |
| Safety Approvals              | • EN60601-1, ANSI/AAMI ES60601-1, CSA22.2 No. 60601-1 per cUL, Including Risk Management, EN60950-1, UL60950-1 (UL1604 Class 1 Div 2 ECM140US12)                                    |

#### Notes

<sup>(1)</sup> Safety approvals cover frequency range 47-63 Hz.

## Models and Ratings – Convection-cooled

ECM140 **XP**

| Output Power <sup>(1)</sup> | Output Voltage V1 | Output Current V1 | Fan Output V2 | Standby Supply V3 <sup>(2)</sup> | Model Number <sup>(2,3)</sup> |
|-----------------------------|-------------------|-------------------|---------------|----------------------------------|-------------------------------|
| 120 W                       | 12.0 VDC          | 10.0 A            | 12.0 V/0.5 A  | 5.0 V/0.5 A                      | ECM140US12                    |
| 120 W                       | 15.0 VDC          | 8.0 A             | 12.0 V/0.5 A  | 5.0 V/0.5 A                      | ECM140US15                    |
| 120 W                       | 18.0 VDC          | 6.6 A             | 12.0 V/0.5 A  | 5.0 V/0.5 A                      | ECM140US18                    |
| 120 W                       | 24.0 VDC          | 5.0 A             | 12.0 V/0.5 A  | 5.0 V/0.5 A                      | ECM140US24                    |
| 120 W                       | 28.0 VDC          | 4.2 A             | 12.0 V/0.5 A  | 5.0 V/0.5 A                      | ECM140US28                    |
| 120 W                       | 48.0 VDC          | 2.5 A             | 12.0 V/0.5 A  | 5.0 V/0.5 A                      | ECM140US48                    |

## Notes

1. Convection-cooled, output power must not exceed 120 W for combined V1, V2, & V3
2. For 5 V standby (V3), Power OK & Inhibit, add suffix '-A' to model number.

3. For covered versions, add suffix '-C' to model number or order part no. ECM140 COVER KIT for standalone cover (see derating curves).  
Not suitable for use in class II installations.

## Models and Ratings – Forced-cooled


| Output Power <sup>(1)</sup> | Output Voltage V1 | Output Current V1 | Fan Output V2 | Standby Supply V3 <sup>(2)</sup> | Model Number <sup>(2)</sup> |
|-----------------------------|-------------------|-------------------|---------------|----------------------------------|-----------------------------|
| 148 W                       | 12.0 VDC          | 11.7 A            | 12.0 V/0.5 A  | 5.0 V/0.5 A                      | ECM140US12                  |
| 148 W                       | 15.0 VDC          | 9.3 A             | 12.0 V/0.5 A  | 5.0 V/0.5 A                      | ECM140US15                  |
| 148 W                       | 18.0 VDC          | 7.7 A             | 12.0 V/0.5 A  | 5.0 V/0.5 A                      | ECM140US18                  |
| 148 W                       | 24.0 VDC          | 5.8 A             | 12.0 V/0.5 A  | 5.0 V/0.5 A                      | ECM140US24                  |
| 148 W                       | 28.0 VDC          | 5.0 A             | 12.0 V/0.5 A  | 5.0 V/0.5 A                      | ECM140US28                  |
| 148 W                       | 48.0 VDC          | 2.9 A             | 12.0 V/0.5 A  | 5.0 V/0.5 A                      | ECM140US48                  |

## Notes

1. 10 CFM airflow achieved with system cooling or with Top Fan assembly.
2. For 5 V standby (V3), Power OK & Inhibit, add suffix '-A' to model number e.g. ECM140US12-A.

3. For cover with Top Fan assembly please refer to longform datasheet for mechanical details.

## Mechanical Details



## Input Connector J1

|             |         |
|-------------|---------|
| Pin 1       | Line    |
| Pin 2       | Neutral |
| .25" Faston | Earth   |

J1 mates with Molex housing 09-50-1031 and Molex series 5194 crimp terminals.

## Output Connector J2

|       |     |
|-------|-----|
| Pin 1 | +V1 |
| Pin 2 | +V1 |
| Pin 3 | +V1 |
| Pin 4 | +V1 |
| Pin 5 | RTN |
| Pin 6 | RTN |
| Pin 7 | RTN |
| Pin 8 | RTN |

J2 mates with Molex housing 09-50-1081 and Molex series 5194 crimp terminals.

## Signal Connector J3

|       |              |        |             |
|-------|--------------|--------|-------------|
| Pin 1 | +5V Standby* | Pin 6  | Inhibit LO* |
| Pin 2 | Logic GND*   | Pin 7  | +Sense      |
| Pin 3 | Logic GND*   | Pin 8  | -Sense      |
| Pin 4 | Power OK*    | Pin 9  | +Vout       |
| Pin 5 | Inhibit HI*  | Pin 10 | -Vout       |

\*Optional

J3 mates with JST housing PHDR-10VS and JST series SPHD-001T-P0.5 crimp terminals.

## Fan Connector J4

|       |             |
|-------|-------------|
| Pin 1 | Fan +(12 V) |
| Pin 2 | Fan -       |

J4 mates with Molex housing 22-01-1024 and Molex series 5103 crimp terminals.

## Notes

1. All dimensions in inches (mm). Tolerance .xx = ±0.02 (0.50); .xxx = ±0.01 (0.25)
2. Weight 0.65 lbs (294 g) approx.
3. Vented cover (see derating curves) dimensions are 5.50 x 3.50 x 1.54 (140 x 89 x 39). See longform datasheet for drawing.

## Derating Curves

See longform datasheet for further information.

