

Wiha Open End Wrenches

Meets DIN 3110 / ISO10102 Specifications




31CRV3 tool steel forgings
Precision formed for an
exact fit

Narrow profile
for better access
in tight locations

Wide I-beam for
better gripping

Satin Chromed
Sure Grip Body

The wrench specified by BMW,
Mercedes & Rolls Royce



350 Open End Wrenches Metric DIN 3110 / ISO 10102

Made from 31CRV3 high performance tool steel. Satin chromed sure grip body. Precision formed for exact fit.

Item No.	mm	mm	OAL	OAL	H	D ¹	D ²		lbs.	pkg.
	mm	mm	mm	Inch	mm	mm	mm			
350 01	4.0 x 5.0	103	4.0	3.3	11.6	13.7	.02	10		
350 02	5.0 x 5.5	104	4.1	3.3	13.7	14.7	.02	10		
350 03	5.5 x 7.0	122	4.8	3.6	15.7	17.7	.04	10		
350 04	6.0 x 7.0	122	4.8	3.6	15.7	17.7	.04	10		
350 05	7.0 x 8.0	130	5.1	3.9	17.7	20.8	.06	10		
350 06	8.0 x 9.0	140	5.5	3.9	20.8	22.9	.07	10		
350 07	8.0 x 10.0	140	5.5	3.9	20.8	22.9	.07	10		
350 08	10.0 x 11.0	156	6.1	4.8	23.9	26.9	.12	10		
350 09	10.0 x 13.0	172	6.7	5.3	24.0	30.0	.15	10		
350 10	12.0 x 13.0	172	6.7	5.3	28.0	31.0	.13	10		
350 11	12.0 x 14.0	172	6.7	5.3	28.0	31.0	.13	10		
350 12	13.0 x 14.0	190	7.5	5.7	32.5	34.9	.20	10		
350 13	14.0 x 15.0	190	7.5	5.7	32.5	34.9	.20	10		
350 14	16.0 x 17.0	204	8.0	5.9	36.1	39.2	.23	10		
350 15	16.0 x 18.0	204	8.0	5.9	36.1	39.2	.23	10		
350 16	18.0 x 19.0	223	8.7	6.5	40.2	42.3	.33	1		
350 17	19.0 x 22.0	236	9.3	6.8	44.9	48.4	.42	1		
350 18	20.0 x 22.0	236	9.3	6.8	44.9	48.4	.41	1		
350 19	21.0 x 23.0	250	9.8	7.3	47.4	51.5	.58	1		
350 20	22.0 x 24.0	250	9.8	7.3	47.4	51.5	.57	1		
350 21	24.0 x 26.0	265	10.4	7.8	52.5	58.6	.70	1		
350 22	24.0 x 27.0	265	10.4	7.8	52.5	58.6	.68	1		
350 23	25.0 x 28.0	280	11.0	8.1	55.2	61.3	.77	1		
350 24	27.0 x 29.0	280	11.0	8.1	58.6	64.4	.79	1		
350 25	27.0 x 30.0	280	11.0	8.1	58.6	64.4	.78	1		
350 26	30.0 x 32.0	302	11.8	8.6	64.8	70.3	1.06	1		
350 27	32.0 x 36.0	325	12.7	8.8	66.5	74.5	1.21	1		
350 28	36.0 x 41.0	358	14.0	8.8	74.5	84.0	1.61	1		
350 29	46.0 x 50.0	450	17.6	10.8	93.5	105.0	3.23	1		

350 Open End Wrenches Inch DIN 3110 / ISO 10102

Made from 31CRV3 high performance tool steel. Satin chromed sure grip body. Precision formed for exact fit.

Item No.	Inch	Inch	OAL	OAL	H	D ¹	D ²		lbs.	pkg.
	Inch	Inch	mm	Inch	mm	mm	mm			
350 32	1/4 x 5/16	190	7.5	5.7	32.5	34.9	.20	10		
350 33	5/16 x 3/8	204	8.0	5.9	36.1	39.2	.23	10		
350 34	3/8 x 7/16	236	9.3	6.8	44.9	48.4	.45	10		
350 35	7/16 x 1/2	250	9.8	7.3	47.4	51.5	.58	10		
350 36	1/2 x 9/16	190	7.5	5.7	32.5	34.9	.20	10		
350 37	9/16 x 5/8	190	7.5	5.7	32.5	34.9	.20	10		
350 38	19/32 x 11/16	204	8.0	5.9	36.1	29.2	.24	10		
350 39	5/8 x 11/16	204	8.0	5.9	36.1	29.2	.23	10		
350 40	5/8 x 3/4	223	8.7	6.5	40.2	42.3	.34	1		
350 41	11/16 x 3/4	223	8.7	6.5	40.2	42.3	.33	1		
350 42	3/4 x 25/32	236	9.3	6.8	44.9	48.4	.42	1		
350 43	3/4 x 7/8	236	9.3	6.8	44.9	48.4	.41	1		
350 44	13/16 x 7/8	236	9.3	6.8	44.9	48.4	.40	1		
350 45	7/8 x 15/16	250	9.8	7.3	47.4	51.5	.57	1		
350 46	15/16 x 1	265	10.4	7.8	52.5	58.6	.68	1		
350 47	1 x 1-1/8	280	11.0	8.1	55.2	61.3	.76	1		
350 48	1-1/16x1-1/4	302	11.8	8.6	59.7	69.9	1.01	1		
350 49	1-1/8x1-5/16	302	11.8	8.6	64.8	70.3	1.06	1		
350 50	1-3/16x1-5/16	302	11.8	8.6	64.8	70.3	1.03	1		
350 51	1-1/4 x 1-3/8	325	12.7	8.8	66.5	74.5	1.22	1		
350 52	1-5/16x1-1/2	325	12.7	8.8	66.5	74.5	1.19	1		
350 53	1-7/16x1-5/8	358	14.0	8.8	74.5	84.0	1.60	1		
350 54	1-1/2 x 1-5/8	358	14.0	8.8	74.5	84.0	1.56	1		
350 55	1-11/16x1-7/8	400	15.7	9.8	84.0	93.5	2.18	1		
350 56	1-13/16 x 2	450	17.6	10.8	93.5	105.0	3.22	1		