


GSD

M39012/20-0504



STAMP: 91836 M39012/20-0504
 KC-59-420,XXXX
 DATE CODE

- NOTES:
- FOR USE WITH RG-58, 141 & 303/U CABLE.
 - FOR CABLING INSTRUCTIONS SEE CP-465.
 - FOR CABLE TRIMMING USE KTJ-123 & KTD-166.
 - FOR CRIMPING USE DIE KTH-2001.
 - INTERFACE PER MIL-STD-348, 301-1.
 - MATERIALS:
 INSULATORS: TEFLON, ASTM-D-1457
 GASKET: SILICONE RUBBER, ZZ-R-765
 K-GRIP SLEEVE: COM BRONZE, ALLOY 220
 OUTER CONTACT } BER. COPPER, ASTM-B-196
 BNC C/C CONTACT F }
 ALL OTHER METAL PARTS: BRASS, ASTM-B16
 - FINISHES:
 CENTER CONTACTS: HARD GOLD PLATE, PER MIL-G-45204
 ALL OTHER METAL PARTS: SILVER PLATE, QQ-S-365
 - ELECTRICAL CHARACTERISTICS:
 NOMINAL IMPEDANCE: 50 OHMS
 WORKING VOLTAGE: 500 VRMS
 FREQUENCY RANGE: DC TO 4 GHz

REVISIONS

ISSUE	CHANGES
9	CN 34481 C REDRAWN KH 04/22/93
10	CN 35064 C JCA 11/22/93
11	CN 39781 C PMC 2/5/07

KAM2728

SCALE 4:1	
APPROX SURFACE AREA	
KC-59-420	
USED ON	
REF:	
PLUG, ANGLE, BNC	
DRAWN KH	DATE 04/22/93
DESIGN MJB	DATE 04/23/93
APPR.	DATE

KINGS
 ELECTRONICS CO., INC.
 ROCK HILL, SOUTH CAROLINA 29730

M39012/20-0504

GSD