



CUSTOMER TERMINAL	RoHS	LEAD(Pb)–FREE
Sn96%, Ag4%	Yes	Yes



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	9–7	●20°C
D.C. RESISTANCE	5–1	●20°C
INDUCTANCE	9–7	60kHz, 1VAC, L _s
LEAKAGE INDUCTANCE	9–7	80kHz, 1VAC, L _s (tie 1+5)
DIELECTRIC	9–5	tie(5+1, 7+9), 1200VDC, 1 second
URNS RATIO	(9–7):(5–1)	20:1, ±3%



REV.	DATE
00	2/09

Packaging Specifications
Method: Tray
PKG-0028
www.midcom-inc.com

Unless otherwise specified:
Tolerances: Fractions: ±1/64
Angles: ±1° Decimals: ±.005[.127]
This drawing is dual dimensioned. Dimensions in brackets are in millimeters.

DRAWING TITLE
TRANSFORMER
eISos p/n: 750340476



REVISIONS: SEE SHEET 1

DRAWING NO.
750340476

SCALE ---

SHEET 2 OF 5